



表 8-1. Function Table

EN	IN1	IN2	NC1/23 TO COM1/23, COM1/23 TO NC1/23	NC4/56 TO COM4/56, COM4/56 TO NC4/56	NO1/23 TO COM1/23, COM1/23 TO NO1/23	NC4/56 TO COM4/56, COM4/56 TO NC4/56
H	X	X	OFF	OFF	OFF	OFF
L	L	L	ON	ON	OFF	OFF
-L	H	L	OFF	ON	ON	OFF
-L	L	H	ON	OFF	OFF	ON
L	H	H	OFF	OFF	ON	ON

- 线阻 50Ω ± 10%
- 最大线长 < 120mm
- 避免在不同信号层走信号线
- 时钟线至少离其他信号线3倍线宽距离
- 数据信号线长差 ≤ 10mm
- 避免时钟线采用蛇形走线, 同时尽量减少数据线上过孔