





R8用于工作在从机状态，工作于主机状态不贴R8
 若工作在主从状态，贴R13，不贴R8和R14
 若工作在从机状态，贴R8和R14，不贴R13
 主机：软启动时间 $T = (0.55 + EA+) C_{SS} / 25ms = 18.3ms$

$KA = R23 / (R22 + R23) = 0.040475$
 $KEF = R21 / (R20 + R21) = 0.3384$

超前臂死区时间 $T_d = 5 * R9 / (0.26 + CS * KA * 1.3) ns =$
 滞后臂死区时间 $T_d = 5 * R10 / (0.26 + CS * KA * 1.3) ns =$
 同步整流管延迟时间 $T_d = 5 * R11 / (2.65 - CS * KEF * 1.32) + 4ns$

最小脉冲宽度 $T_{MIN} = (5.92 * R12) ns = 76.96ns$

工作于峰值电流模式：贴R15，不贴R7
 工作于电压模式：贴R7，不贴R15



Title		
Size	Number	Revision
A4		
Date:	2018/9/26	Sheet of
File:	F:\KuGou\...\PSFB Driver-UCC28951-Q1\1.0.SchDoc	