

### Navigator

Sequence: Sequence 1

- FFT测试模板
  - Sequencer Properties...
  - Pre-Sequence Steps
    - 非平衡信号 4欧姆 低音
    - 平衡信号 8欧姆 高音
    - 平衡信号 4欧姆 高音
    - 平衡信号 4欧姆 低音
  - 信号设置
    - Measurement Sequence Settings...
      - Sequence Steps
        - RMS Level
        - THD+N Ratio
        - EQ模式 频率曲线
        - 模式 频率曲线
        - SNR
        - 功率 THD
        - Noise Recorder (RMS)
      - Add Measurement...
      - 蓝牙测试
      - Add Signal Path
    - Post-Sequence Steps
      - Add Step...

### Monitors/Meters

	Level	THD+N	Frequency
Ch1	305 mVrms	0.011 %	1.000 kHz

### Input/Output

#### Output Configuration

Connector: Analog Balanced  
Channels: 1  
EQ: None

#### Input Configuration

Connector: Analog Balanced  
Channels: 1  
Channel: Ch1  
Termination: 200 kohm

#### Verify Connections

Generator: ON  
Waveform: Sine  
Test Channel: All Channels  
Level: 0.000 dBu  
Frequency: 1.00000 kHz  
DC Offset: 0.000 V

