






Zdiff=100ohm
less than two vias



Note:
1. The HDMI impedance is 100R

I2C EN	MODE
L	Pin Strap Mode
H	I2C Control Mode

I2C EN = Low	MODE
PRE	Pre-emphasis
L	0 dB
H	3.5dB

EQ2	EQ1	RK	EQ
L	L	L	2dB
L	Z	L	3dB
L	H	L	5dB
Z	L	Z	6.5dB
Z	Z	Z	8.5dB
Z	H	Z	10dB
H	L	H	11dB

Resistor	MODE
6K	HDMI and DP combination
6.49K	HDMI

SLEW	Clock Slew Rate
L	203 ps
H	122 ps
NC	1 ~ 180 ps

