



NOTE

DSP_BOARD_12V---->TPS_DSP_5V
 DSP_BOARD_12V---->TPS_DSP_3V3

$$V_O = 0.8 * (R1 + R2) / R2$$

R1	R2	V _O
40.2K	7.5K	5.1V
40.2K	12.7K	3.3V

$$R_{OSC} (K) = 1.74 * F (MHZ)^{-1.122}$$

383K 500KHZ