





Bill of Materials

<Parameter Title not found>

Source Data From: PCB_Project1.PrjPCB
 Project: PCB_Project1.PrjPCB
 Variant: None

Creation Date: 2013-3-21 上午 10:40:54

Print Date: 41354 41354.4452

Footprint	Comment	LibRef	Designator	Description	Quantity
RC1	1uF	CAP	C1, C3, C5, C7, C8, C15, C21	Capacitor	7
RC2	47uf	CAP	C2, C4	Capacitor	2
RC2	10uf	CAP, CAPACITOR POL, ELECTRO1	C6, C10, C14, C19	Capacitor	4
RC1	0.01uf	CAP	C9	Capacitor	1
RC1	27pF	CAP	C11, C20, CG0, CG1, CG2	Capacitor	5
RC1	0.1uF	CAP	C12, C13	Capacitor	2
RC1	200p	CAP	C17		1
RC1	56p	CAP	C18		1
RC2	10u	CAP	C22, C24, C25		3
RC2	22u	CAP	C23		1
CAPMP5918 X18N		DIODE	D1, D3, D5, D6	Diode	4
TAN	MBRS0540	DIODE SCHOTTKY	D2	Schottky Diode	1
CC-DIODE	Control-Current Diode	DIODE	D4	Diode	1
SIP7	CON7	CON7	J1	Connector	1
SIP2	CON2	CON2	J2, J3	Connector	2
DIANGAN	220uH	INDUCTOR, INDUCTOR2	L1, L2, L3, L4		4
RC1	0	RES2	R0, RG0, RG1, RG2, RG3, RG4, RG5		7
RC1	1K	RES2	R1, Rdiv		2
RC1	4.02K	RES2	R2		1
RC1	9.09K	RES2	R3		1
RC1	19.10K	RES2	R4		1
RC1	49.90K	RES2	R5		1
RC1	73.2K	RES2	R6		1
RC1	100K	RES2	R7, R13		2
RC1	510k	RES2	R9		1
RC1	30k	RES2	R12		1
RC1	5.6K	RES2	R14		1
RC1	6.8K	RES2	R15		1
RC1	24.9K	RES2	R16, R22		2
RC1	Res2	Res2	R17, R18	Resistor	2
RC1	200K	RES2	R19		1
RC1	49.9K	RES2	R20		1
RC1	22K	RES2	R21		1
RC1	20	RES2	R23, R24		2
RC1	30	RES2	R25		1
2985	LP2985	LP2985	U1		1
max1606	MAX1606	MAX1606	U2		1
SMD8A	OPA2350	OPA2340	U4		1
max4638	MAX4638(1)	HEADER 8X2	U5		1
SMD8A	OPA2340	OPA2340	U6		1

Approved	Notes