

Title		
Size	Number	Revision
A4		
Date:	2011-11-2	Sheet of
File:	E:\pcb\	10.21 .SchDown By:

1

2

3

4

1


2

3

4

67.945 (mm)

46.99 (mm)



Comment	Description	Designator	Footprint	LibRef	Quantity
	Capacitor	C1, C2, C4, C5, C7, C8, C9, C14, C16, C17	.1C	Cap	10
Cap Pol2	Polarized Capacitor (Axial)	C3, C6, C11, C13, C15	1206CC	Cap Pol2	5
	Capacitor	C10	0805C	Cap	1
Cap	Capacitor	C12	.1C	Cap	1
Header 2	Header, 2-Pin	P1	IDC---2	Header 2	1
Header 12	Header, 12-Pin	P2	IDC--12	Header 12	1
Header 2	Header, 2-Pin	P3	1206R	Header 2	1
Header 2	Header, 2-Pin	P4	HDR1X2	Header 2	1
	Resistor	R1, R2, R4, R5, R6, R7, R8, R9, R10	1206R	Res2	9
Res Tap	Tapped Resistor	R3	R503	Res Tap	1
传感器		U1	guangdianchi	传感器	1
OPA121KM	Low-Cost Precision Difet Operational Amplifier	U2	SOP8	OPA121KM	1
3.68640M		U3	XJO	XTAL	1
ADS1253E		U4	SSOP-16	ADS1253	1
OPA350	High-Speed, Single-Supply, Rail-to-Rail OPERATIONAL AMPLIFIERS	U5	SOP-8	OPA350	1
REF3040	Voltage Regulator	VR1	SOT23-3	Volt Reg	1