

C

Defaul t 1.8V

MIPI TO LVDS

0ohm-0402-5%-1/16W



10-E 0805 YEP 20% 16V

100F-0805-X5R-20%-16V
100F-0805-X5R-20%-16V

0.1uF-0402-X7R-10%-16V


陶瓷电容,CAP MC,50V,0.01uF,10%,X7R,0402,SMD,TP

陶瓷电容,CAP MC,50V,0.01uF,10%,X7R,0402,SMD,TP



SN65DI84 I2C地址: 0x2D

LVDS转换芯片,IC LVDS,MIPI to Dual LVDS,PBGA-64,SMD,SN65DSI84ZQER,TI



金针, pin connector, 215Pin/without pin6, D, D2.0, L=1.9mm, SMD, LD