


REV	DATE	RECORD	DESIGN	CHK
2	10/14/2019	PROTOTYPE REL	AGC	JEL
3	01/15/2020	Change L1 to 100uh, trace to R2, R1 to 390K	FDP	AGC
4	06/10/2020	Revisions based on Validation Testing	AGC	AGC



This document contains confidential and proprietary information of Dual-Lite. Receipt or possession of this document does not convey any rights to reproduce or disclose its contents, or to make, use, or sell anything it may disclose. Reproduction, disclosure, or use of the document or its contents, without the specific written authorization of Dual-lite, may violate the intellectual property rights of Dual-Lite.

UNSPECIFIED TOLERANCE: INCHES
X.X=±0.02 X.XX=±0.02 X.XXX=±0.010
FRACTIONS=±1/64 ANGULAR TOLERANCE=±1/2°

DIMENSIONS IN INCHES
DIMENSIONS IN [] IN MM
CONFORMS TO ASME Y14.5M
DO NOT SCALE PRINT



DRAWN BY: AGC
CHECKED BY: *
ENGINEERING: AGC
SCALE: NTS
SIZE: A



701 Millennium Blvd.
Greenville, SC 29607
(864) 678-1000

SCH ELSS REMOTE
OUTDOOR HEAD

PART NO: 93109375

DRAWING NO.:
93109375-0000

REV.: 3
SHT 1
1 SHTS