






U\_TO MCU  
TO MCU.SchDoc

U\_USB and BT audio  
USB and BT audio.SCHDOC



U\_DIR  
DIR.SCHDOC



U\_AUX Bridge  
AUX Bridge.SCHDOC



repeat(U\_ES9039Q2M\_DAC.1,2)  
ES9039Q2M\_DAC.SCHDOC





ADDR1/HW2/SS1  
ADDR1/HW2/SS2





repeat(U\_Output Stage.1,2)  
Output Stage.SCHDOC




VOL\_CS1  
VOL\_CS2



U\_Power Supplies  
Power Supplies.SCHDOC




Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\First Sheet.SCHDOC	Drawn By:




- 并联（硬件）模式：
- 1、PSN: H, 设为硬件模式
  - 2、IPSO: I, IPSI 设置输入通道选择
  - 3、DIF0 设置数据格式, 101 为 24bit I2S
  - 4、P2 的 3 脚与 8 脚相连, J2 的 2 脚与 1 脚相连, 让 OSK0 和 OSK 1 连接至 SW1, 并将 SW1 对应 OSK 位下拉
  - 5、CM0 和 CM1 设置时钟源, 默认 CM0=1, CM1=0.
  - 6、XTL0 和 XTL1 应该设为 0, 适应 11.2896M 晶振

Title		Revision	
Size	Number		
A2			
Title	20240208	Sheet of	
File	FSDAC零件1-PCB_LAYOUT_SCHDOC	Drawn By:	




Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\USB and BT audio.SCHDOC	Drawn By:






	J8	J9	U15		U16	
			A0	A1	A0	A1
USB Audio	0	0	0	0	0	0
DIR	1	0	1	0	1	0
BlueTooth Audio	0	1	0	1	0	1

U15: A0=0,A1=0





Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\LAUX Bridge.SCHDOC	Drawn By:










Title		
Size	Number	Revision
A2		
Date:	20240508	Sheet of
File:	F3DAC零件1.Pcb/Output Stage Schematic	Drawn By:




Title		
Size	Number	Revision
A2		
Date:	20240508	Sheet of
File:	FSDAC零件1.PLT_Power Supplies SCHDOC	Drawn By:




- R172 56kΩ (5602) ±1%
- HA.LOUT+ 56kΩ (5602) ±1%
- HA.LOUT- 56kΩ (5602) ±1%
- HA.ROUT+ 56kΩ (5602) ±1%
- HA.ROUT- 56kΩ (5602) ±1%
- HA.SE.L 56kΩ (5602) ±1%
- HA.SE.R 56kΩ (5602) ±1%
- R178 56kΩ (5602) ±1%
- R179 56kΩ (5602) ±1%
- R180 56kΩ (5602) ±1%


Title		Revision	
Size	A2	Number	
Date	2/24/2026	Sheet of	8
File	F:\DOC 零件工程\Headphone amp16	Drawn by	



Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\MCLK.SchDoc	Drawn By:



Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\RCA OUT.SchDoc	Drawn By:



Title		
Size	Number	Revision
A3		
Date:	2/24/2026	Sheet of
File:	F:\DAC硬件工程\TO MCU\SchDoc	Drawn By: