

**Conducted Emission Measurement**


File :CE0204

Data :#1

Date: 2021-2-4

Time: 10:49:31

100.0 dBuV



Site

Phase: **L1**

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 5V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.1740	24.99	9.56	34.55	64.76	-30.21	peak	
2	*	0.5620	26.89	9.55	36.44	56.00	-19.56	peak	
3		0.5620	16.56	9.55	26.11	46.00	-19.89	AVG	
4		1.6220	24.11	9.58	33.69	56.00	-22.31	peak	
5		1.6860	10.34	9.58	19.92	46.00	-26.08	AVG	
6		14.9900	21.91	9.77	31.68	60.00	-28.32	peak	
7		15.1420	13.13	9.77	22.90	50.00	-27.10	AVG	

\*:Maximum data    x:Over limit    !:over margin

Conducted Emission Measurement


File :CE0204

Data :#2

Date: 2021-2-4

Time: 10:52:23

100.0 dBuV



Site

Phase: **N**

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 5V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.6020	32.48	9.54	42.02	56.00	-13.98	peak	
2	*	0.6020	24.75	9.54	34.29	46.00	-11.71	AVG	
3		1.0300	20.99	9.55	30.54	46.00	-15.46	AVG	
4		2.2700	24.99	9.57	34.56	56.00	-21.44	peak	
5		2.4100	17.41	9.57	26.98	46.00	-19.02	AVG	
6		7.3060	13.45	9.65	23.10	50.00	-26.90	AVG	
7		8.0580	26.46	9.66	36.12	60.00	-23.88	peak	

\*:Maximum data x:Over limit !:over margin

Conducted Emission Measurement


File :CE0204

Data :#3

Date: 2021-2-4

Time: 11:07:23

100.0 dBuV



Site

Phase: -

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 12V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.1500	44.77	9.55	54.32	65.99	-11.67	peak	
2		0.1539	29.94	9.55	39.49	55.78	-16.29	AVG	
3		0.3060	21.08	9.53	30.61	50.08	-19.47	AVG	
4	X	0.7700	48.46	9.54	58.00	56.00	2.00	peak	
5	*	0.7700	47.05	9.54	56.59	46.00	10.59	AVG	
6		1.3940	33.26	9.55	42.81	56.00	-13.19	peak	
7		1.5420	29.11	9.57	38.68	56.00	-17.32	peak	
8		1.5460	27.65	9.57	37.22	46.00	-8.78	AVG	
9		10.7940	28.60	9.70	38.30	60.00	-21.70	peak	
10		12.1980	24.82	9.72	34.54	50.00	-15.46	AVG	

\*:Maximum data x:Over limit !:over margin

### Conducted Emission Measurement


File :CE0204

Data :#4

Date: 2021-2-4

Time: 11:09:26

100.0 dBuV



Site

Phase: +

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 12V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.1539	30.31	9.56	39.87	55.78	-15.91	AVG	
2		0.1660	44.11	9.56	53.67	65.15	-11.48	peak	
3	X	0.7700	54.47	9.55	64.02	56.00	8.02	peak	
4	*	0.7700	47.30	9.55	56.85	46.00	10.85	AVG	
5		1.5420	28.89	9.58	38.47	56.00	-17.53	peak	
6		1.5420	27.60	9.58	37.18	46.00	-8.82	AVG	
7		10.7940	29.49	9.71	39.20	60.00	-20.80	peak	
8		11.8940	25.03	9.73	34.76	50.00	-15.24	AVG	

\*:Maximum data    x:Over limit    !:over margin

**Conducted Emission Measurement**


File :CE0204

Data :#5

Date: 2021-2-4

Time: 11:12:51

100.0 dBuV



Site

Phase: +

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 24V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.1539	47.17	9.56	56.73	65.78	-9.05	peak	
2		0.1539	22.43	9.56	31.99	55.78	-23.79	AVG	
3	X	0.7700	47.68	9.55	57.23	56.00	1.23	peak	
4	*	0.7700	45.51	9.55	55.06	46.00	9.06	AVG	
5		1.5460	33.46	9.58	43.04	56.00	-12.96	peak	
6		1.5460	31.86	9.58	41.44	46.00	-4.56	AVG	
7		12.1980	28.52	9.73	38.25	60.00	-21.75	peak	
8		12.1980	25.07	9.73	34.80	50.00	-15.20	AVG	

\*:Maximum data    x:Over limit    !:over margin

### Conducted Emission Measurement


File :CE0204

Data :#6

Date: 2021-2-4

Time: 11:14:49

100.0 dBuV



Site

Phase: -

Temperature: 23.5

Limit: EN55032\_Class B\_(0.15-30MHz) \_Main\_QP

Power: DC 24V

Humidity: 45 %

EUT: 诊断仪

M/N: IVD630

Mode: Working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.1539	21.72	9.55	31.27	55.78	-24.51	AVG	
2		0.1900	42.17	9.54	51.71	64.03	-12.32	peak	
3	X	0.7740	47.84	9.54	57.38	56.00	1.38	peak	
4	*	0.7740	46.08	9.54	55.62	46.00	9.62	AVG	
5		1.5460	40.09	9.57	49.66	56.00	-6.34	peak	
6		1.5460	32.57	9.57	42.14	46.00	-3.86	AVG	
7		11.9540	23.74	9.72	33.46	50.00	-16.54	AVG	
8		12.1980	27.95	9.72	37.67	60.00	-22.33	peak	

\*:Maximum data    x:Over limit    !:over margin