

Radiated Emission Measurement


File :RE0207

Data :#3

Date: 2021-2-7

Time: 13:37:58

72.0 dBuV/m



Site

Polarization: **Horizontal**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 12V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	Antenna Height	Table Degree	
		MHz	dBuV	dB	dBuV/m	dBuV/m	dB	cm	degree	Comment
1		155.3644	13.20	11.61	24.81	40.00	-15.19			peak
2		250.3012	14.71	13.48	28.19	47.00	-18.81			peak
3		560.6928	14.28	22.32	36.60	47.00	-10.40			peak
4	*	890.7278	10.55	26.38	36.93	47.00	-10.07			peak

*:Maximum data x:Over limit !:over margin

Radiated Emission Measurement


File :RE0207

Data :#4

Date: 2021-2-7

Time: 13:40:08

72.0 dBuV/m



Site

Polarization: **Vertical**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 12V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	Antenna Height	Table Degree	
		MHz	dBuV	dB	dBuV/m	dBuV/m	dB	cm	degree	Comment
1	*	30.0000	10.29	18.84	29.13	40.00	-10.87			peak
2		100.2286	16.66	11.07	27.73	40.00	-12.27			peak
3		152.6641	12.91	11.82	24.73	40.00	-15.27			peak
4		560.6928	12.46	22.32	34.78	47.00	-12.22			peak

*:Maximum data x:Over limit !:over margin

Radiated Emission Measurement


File :RE0207

Data :#5

Date: 2021-2-7

Time: 13:42:01

72.0 dBuV/m



Site

Polarization: **Vertical**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 12V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dBuV/m	Over dB	Antenna Height cm	Table Degree degree	Comment
1	*	30.3173	11.04	18.68	29.72	40.00	-10.28	peak		
2		45.6948	16.87	10.87	27.74	40.00	-12.26	peak		
3		92.1388	11.99	10.15	22.14	40.00	-17.86	peak		
4		147.9214	13.49	12.00	25.49	40.00	-14.51	peak		
5		601.4265	10.99	21.74	32.73	47.00	-14.27	peak		

*:Maximum data x:Over limit !:over margin

Radiated Emission Measurement


File :RE0207

Data :#6

Date: 2021-2-7

Time: 13:44:06

72.0 dBuV/m



Site

Polarization: **Horizontal**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 12V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	Antenna Height	Table Degree	
		MHz	dBuV	dB	dBuV/m	dBuV/m	dB	cm	degree	Comment
1		110.5687	13.27	11.35	24.62	40.00	-15.38			peak
2		157.5588	14.87	11.23	26.10	40.00	-13.90			peak
3		280.0237	11.24	16.00	27.24	47.00	-19.76			peak
4	*	560.6928	12.32	22.32	34.64	47.00	-12.36			peak

*:Maximum data x:Over limit !:over margin

Radiated Emission Measurement


File :RE0207

Data :#7

Date: 2021-2-7

Time: 13:47:19

72.0 dBuV/m



Site

Polarization: **Horizontal**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 5V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dBuV/m	Over dB	Antenna Height cm	Table Degree degree	Comment
1		76.7808	12.79	7.46	20.25	40.00	-19.75			peak
2	*	149.4857	19.71	11.98	31.69	40.00	-8.31			peak
3		340.7817	13.87	16.19	30.06	47.00	-16.94			peak
4		560.6928	14.08	22.32	36.40	47.00	-10.60			peak

*:Maximum data x:Over limit !:over margin

Radiated Emission Measurement


File :RE0207

Data :#8

Date: 2021-2-7

Time: 13:48:19

72.0 dBuV/m



Site

Polarization: **Vertical**

Temperature: 25.2

Limit: EN55032_B_30-1000MHz_Radiated_QP

Power: DC 5V

Humidity: 55 %

EUT: 汽车电脑智能诊断仪

Distance: 3m

M/N: IVD630

Mode: working

Note:

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	Antenna Height	Table Degree	
		MHz	dBuV	dB	dBuV/m	dBuV/m	dB	cm	degree	Comment
1		38.6160	15.00	14.62	29.62	40.00	-10.38			peak
2		68.6310	21.59	6.07	27.66	40.00	-12.34			peak
3	*	153.7385	20.21	11.76	31.97	40.00	-8.03			peak
4		560.6928	12.88	22.32	35.20	47.00	-11.80			peak

*:Maximum data x:Over limit !:over margin