

SDNT1005X103F3435FTF R-T对照表

温度 (℃)	25℃ 阻值 (K Ω)	B值	阻值 (K Ω)	温度 (℃)	25℃ 阻值 (K Ω)	B值	阻值 (K Ω)	温度 (℃)	25℃ 阻值 (K Ω)	B值	阻值 (K Ω)	温度 (℃)	25℃ 阻值 (K Ω)	B值	阻值 (K Ω)
-30	10	3435	119.52	8	10	3435	19.70	46	10	3435	4.72	84	10	3435	1.48
-29	10	3435	113.30	9	10	3435	18.90	47	10	3435	4.57	85	10	3435	1.44
-28	10	3435	107.45	10	10	3435	18.13	48	10	3435	4.42	86	10	3435	1.40
-27	10	3435	101.93	11	10	3435	17.39	49	10	3435	4.27	87	10	3435	1.37
-26	10	3435	96.73	12	10	3435	16.69	50	10	3435	4.13	88	10	3435	1.33
-25	10	3435	91.83	13	10	3435	16.02	51	10	3435	4.00	89	10	3435	1.29
-24	10	3435	87.21	14	10	3435	15.39	52	10	3435	3.87	90	10	3435	1.26
-23	10	3435	82.85	15	10	3435	14.78	53	10	3435	3.75	91	10	3435	1.23
-22	10	3435	78.73	16	10	3435	14.20	54	10	3435	3.63	92	10	3435	1.19
-21	10	3435	74.85	17	10	3435	13.64	55	10	3435	3.51	93	10	3435	1.16
-20	10	3435	71.18	18	10	3435	13.11	56	10	3435	3.40	94	10	3435	1.13
-19	10	3435	67.71	19	10	3435	12.61	57	10	3435	3.30	95	10	3435	1.10
-18	10	3435	64.43	20	10	3435	12.12	58	10	3435	3.19	96	10	3435	1.07
-17	10	3435	61.33	21	10	3435	11.66	59	10	3435	3.09	97	10	3435	1.05
-16	10	3435	58.40	22	10	3435	11.22	60	10	3435	3.00	98	10	3435	1.02
-15	10	3435	55.62	23	10	3435	10.79	61	10	3435	2.91	99	10	3435	0.99
-14	10	3435	53.00	24	10	3435	10.39	62	10	3435	2.82	100	10	3435	0.97
-13	10	3435	50.51	25	10	3435	10.00	63	10	3435	2.73	101	10	3435	0.95
-12	10	3435	48.16	26	10	3435	9.63	64	10	3435	2.65	102	10	3435	0.92
-11	10	3435	45.93	27	10	3435	9.27	65	10	3435	2.57	103	10	3435	0.90
-10	10	3435	43.81	28	10	3435	8.93	66	10	3435	2.49	104	10	3435	0.88
-9	10	3435	41.81	29	10	3435	8.61	67	10	3435	2.42	105	10	3435	0.85
-8	10	3435	39.91	30	10	3435	8.30	68	10	3435	2.35	106	10	3435	0.83
-7	10	3435	38.11	31	10	3435	8.00	69	10	3435	2.28	107	10	3435	0.81
-6	10	3435	36.40	32	10	3435	7.71	70	10	3435	2.21	108	10	3435	0.79
-5	10	3435	34.77	33	10	3435	7.43	71	10	3435	2.15	109	10	3435	0.77
-4	10	3435	33.23	34	10	3435	7.17	72	10	3435	2.09	110	10	3435	0.76
-3	10	3435	31.77	35	10	3435	6.92	73	10	3435	2.03	111	10	3435	0.74
-2	10	3435	30.38	36	10	3435	6.67	74	10	3435	1.97	112	10	3435	0.72
-1	10	3435	29.05	37	10	3435	6.44	75	10	3435	1.91	113	10	3435	0.70
0	10	3435	27.80	38	10	3435	6.22	76	10	3435	1.86	114	10	3435	0.69
1	10	3435	26.60	39	10	3435	6.00	77	10	3435	1.80	115	10	3435	0.67
2	10	3435	25.46	40	10	3435	5.80	78	10	3435	1.75	116	10	3435	0.65
3	10	3435	24.38	41	10	3435	5.60	79	10	3435	1.70	117	10	3435	0.64
4	10	3435	23.35	42	10	3435	5.41	80	10	3435	1.66	118	10	3435	0.62
5	10	3435	22.37	43	10	3435	5.23	81	10	3435	1.61	119	10	3435	0.61
6	10	3435	21.44	44	10	3435	5.05	82	10	3435	1.57	120	10	3435	0.60
7	10	3435	20.55	45	10	3435	4.88	83	10	3435	1.52	125	10	3435	0.53

