

0 N/A N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	14.8274 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-14.8643 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-1.1533 mV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	6.1518 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	6.1649 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	-13.1514 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1641 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1628 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	71.2066 dB	(F) N/A	0.0000	0

Site Failed tests/Executed tests

0 1 9

Site Sort Bin

0 N/A N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	14.8673 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-14.8912 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-1.1555 mV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	6.1459 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	6.1613 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	-15.4040 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1648 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1641 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	71.2268 dB	(F) N/A	0.0000	0

Site Failed tests/Executed tests

0 1 9

Site Sort Bin

0 N/A N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	15.2104 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-15.2493 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-1.1376 mV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	7.3655 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	7.4128 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	-47.3156 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1665 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1561 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	71.1296 dB	(F) N/A	0.0000	0

Site Failed tests/Executed tests

0 1 9

Site Sort Bin

0 N/A N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									

Datalog report
09/10/2020 20:01:30
Prog Name: F4151A.xls
Job Name: F4151A.xls
Lot:
Operator: Administrator
Test Mode:
Node Name: MF6390
Part Type:
Channel map: Chans
Environment:

Site Number:
0

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	14.7405 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-14.7593 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-1.1791 mV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	6.3953 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	6.3761 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	19.1305 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1644 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1620 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	71.1596 dB	(F) N/A	0.0000	0

Site Failed tests/Executed tests

0	1	9
Site	Sort	Bin
0	N/A	N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	14.6817 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-14.7087 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-705.5176 uV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	7.7622 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	7.7916 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	-29.4102 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1607 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1510 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	74.1226 dB	(F) N/A	0.0000	0

Site Failed tests/Executed tests

0	1	9
Site	Sort	Bin
0	N/A	N/A

Device#: 0

Number	Site	Test Name	Pin	Channel	Low	Measured	High	Force	Loc
<IS>									
0	0	Icc	vcc_pos	10. a8	0.0000 A	14.7405 mA	21.0000 mA	0.0000	0
1	0	Iee	vcc_neg	10. a12	-21.0000 mA	-14.7593 mA	0.0000 A	0.0000	0
<Vos>									
2	0	vos	out		-7.0000 mV	-1.1791 mV	7.0000 mV	0.0000	0
<IB>									
3	0	IB	in_pos	14. a37	N/A	6.3953 uA	15.0000 uA	0.0000	0
4	0	IB	in_neg	14. d37	N/A	6.3761 uA	15.0000 uA	0.0000	0
5	0	Ios	in_pos	14. a37	N/A	19.1305 nA	1.2000 uA	0.0000	0
<Vo>									
6	0	Vo+	out		11.6000 V	14.1644 V	15.0000 V	0.0000	0
7	0	Vo-	out		-15.0000 V	-14.1620 V	-11.6000 V	0.0000	0
<CMRR>									
8	0	CMRR	out		75.0000 dB	71.1596 dB	(F) N/A	0.0000	0

温度、湿度检测记录

Q/WD.JL.6.4.2

2010 年度: 北测 试间

高可靠产品研究所

工 序																	检测人
标准 日期		温 度	湿度	结 论	温 度	湿度	结 论	温 度	湿度	结 论	温 度	湿度	结 论	温 度	湿度	结 论	
		℃	%		℃	%		℃	%		℃	%		℃	%		
7	1	25	42	正常	26	41	正常		7	16	25	43	正常	26	42	正常	李霞
7	2	25	41	正常	25	42	正常		7	17	26	42	正常	25	41	正常	李霞
7	3	25	39	正常	26	42	正常		7	18	25	41	正常	26	43	正常	李霞
7	4	26	41	正常	25	41	正常		7	19	24	40	正常	25	42	正常	李霞
7	5	25	42	正常	25	40	正常		7	20	26	43	正常	25	39	正常	李霞
7	6	26	41	正常	26	42	正常		7	21	25	42	正常	26	44	正常	李霞
7	7	25	42	正常	25	40	正常		7	22	26	43	正常	25	43	正常	李霞
7	8	25	41	正常	25	41	正常		7	23	25	41	正常	24	43	正常	李霞
7	9	25	43	正常	25	42	正常		7	24	26	42	正常	26	42	正常	李霞
7	10	26	44	正常	26	43	正常		7	25	25	41	正常	25	41	正常	李霞
7	11	24	40	正常	25	42	正常		7	26	26	42	正常	26	42	正常	李霞
7	12	26	42	正常	26	41	正常		7	27	25	41	正常	25	43	正常	李霞
7	13	25	41	正常	24	43	正常		7	28	26	43	正常	26	42	正常	李霞
7	14	25	42	正常	24	42	正常		7	29	25	42	正常	24	43	正常	李霞
7	15	25	43	正常	25	43	正常		7	30	26	41	正常	26	43	正常	李霞
									7	31	26	42	正常	25	41	正常	李霞