



使用EE19 (PC40) 磁芯, 立式骨架。
 源边1-2PIN脚使用单股Φ0.35mm的铜线并绕,
 匝数为79, 电感量为590uH±10%;
 4-5PIN使用单股Φ0.2mm的铜线, 匝数为15;
 6-10PIN使用3股Φ0.35mm的铜线并绕, 匝数为15;

Title		
Size A4	Number	Revision
Date: 2013-10-15	Sheet of	
File: Sheet1.SchDoc	Drawn By:	