

CUSTOMER

P/N

REV.

PAGE

DRAW NO.


S/N

A

1/4

0

1. DIMENSION



NOTE:

1. PIN 2,4,6,7,9,11 CUT OFF.
2. "XXXX" 表示年和周期; 并显示在顶部
3. 研磨CORE置于頂端.
4. 兩端CORE均須加工2層.(如圖示)
5. 產品中柱點#508白膠, 結合處點四點黑膠, 并裝鐵夾固定.
6. 成品沿線包包0.025mm/t(自粘性銅箔)1TS, 引線為0.32mm接PIN1.
7. 外圍先沿CORE包TAPE 1TS, 再沿線包包TAPE 1TS.

REPORTED

CHECKED

APPROVED





CUSTOMER	P/N	REV.	PAGE	DRAW NO.
	S/N	A	4/4	0

4. MATERIAL LIST:

NO	ITEM	SIZE	MATERIAL	RATING	MANUFACTURER	UL FILE NO
1.	BOBBIN	RM12	PHENOLIC T375J 94V-0	150°C		E59481
2.	CORE	FERRITE CORE RM12	TP4 PC44 PL9 PF-2L		TDG CO. , TDK CO. , SAMWHA CO. , CWGC CO. ,	
3.	WIRE	0.15 mm 0.5mm	POLYURETHANE ENAMELLED WIRE	130°C 130°C		E84081 E106004
		0.4mm	TRIPLE INSULATION WIRE	130°C		E303298
4.	TAPE	0.025mm	#1350F-1	130°C	3M CO. ,	E17385
5.	MARGIN TAPE		#44	130°C	3M CO. ,	E17385
6.	VARNISH		BC-346A	200°C		E51047
7.	TUBE		TFLON TUBE TFL	200°C		E156256
8.	COPPER	0.025mm/t				
9.	EPOXY		6020H	260°C		E229633
			#508			E108491