








Title		
Size	Number	Revision
A4		
Date:	2014-6-24	Sheet of
File:	E:\Altium Designer\...\Sheet1.SchDoc	Drawn By:



Title		
Size	Number	Revision
A4		
Date:	2014-6-24	Sheet of
File:	E:\Altium Designer\Sheet2.SchDoc	Drawn By:

Comment	Description	Designator	Footprint	LibRef	Quantity
1uf	1uf/0603/10%/25V	C1, C3, C16, C17, C25	C0603	C0603/1uf/10%/25V	5
0.1uf	100nf/0603/10%/50V	C2, C4, C12, C18, C19, C21, C24, C30, C33, C37, C38, C39, C40, C43, C44, C45, C51, C52	C0603	C0603/100nf/10%/50V	18
NI	470nf/0603/10%/25V	C5, C7, C11, C15, C22	C0603	C0603/470nf/10%/25V	5
1.5nf	470nf/0603/10%/25V	C6	C0603	C0603/470nf/10%/25V	1
47pf	47pf/0603/10%/50V	C8, C9	C0603	C0603/47pf/10%/50V	2
4.7nf	470nf/0603/10%/25V	C10, C14	C0603	C0603/470nf/10%/25V	2
2.2nf	2.2nf/0603/X/X	C13, C20, C26, C27	C0603	C0603/2.2nf/10%/50V	4
10uf	10uf/0805/10%/10V	C23, C29, C32, C35, C36, C41, C46	C0805	C0805/10uf/10%/10V	7
2.2uf	1uf/0603/10%/25V, 470nf/0603/10%/25V	C28, C34	C0603	C0603/1uf/10%/25V, C0603/470nf/10%/25V	2
10nf	10nf/0603/10%/50V	C31	C0603	C0603/10nf/10%/50V	1
100uf	100uf/25V	C42	CAPA630X770N	C_Aluminum_100uf	1
22pf	22pf/0603/5%/50V	C47, C48	C0603	C0603/22pf/5%/50V	2
10pf	10pf/0603/5%/50V	C49, C50	C0603	C0603/10pf/5%/50V	2
1N5819	1N5819HW/40V/1A/SOD123	D1, D2	DO035X015	1N5819HW/40V/1A/SOD123	2
LED 插立		D3	D-LED3	LED 插立	1
100M/120	磁珠 /100M/120/060	FB1, FB2, FB3	FB0603	FB0603/100M/120	3
5pin/2.0mm/LT	5pin/2.0mm/ 立	J1	CON5X1LT200	CON5X1LT200	1
PI-320B		J2	PI-320B	Earphone	1
4pin/1.5mm/LT	4pin/1.5mm/ 立	J3, J4	CON4X1LT150	CON4X1LT150	2
HC735		O1		HC735	1
MMBT3904	MMBT3904/40V/200mA/SOT-23/NPN	Q1	SOT95P240X110-3N	NPN/MMBT3904/40V/200mA/SOT-23	1
NI	0603/X/0R/X/(X)	R1, R11, R25, R29, R43	R0603	R0603/X/0R/X/(X)	5
100K	0603/50ppm/100K/1%/(1/16W)	R2, R7	R0603	R0603/50ppm/100K/1%/(1/16	2
10K	0603/50ppm/10K/1%/(1/16W)	R3, R4, R5, R6, R27, R40, R41, R46, R47, R48	R0603	R0603/50ppm/10K/1%/(1/16W)	10
51K	0603/100ppm/51K/1%/(1/16W)	R8, R14	R0603	R0603/100ppm/51K/1%/(1/16	2
0R	0603/X/0R/X/(X)	R9, R10, R12, R13, R15, R16, R17, R18, R26, R32, R33, R34	R0603	R0603/X/0R/X/(X)	12
1M	0603/50ppm/1M/1%/(1/16W)	R19, R23, R24, R28, R42	R0603	R0603/50ppm/1M/1%/(1/16W)	5
5.1K	0603/50ppm/5.1k/1%/(1/16W)	R20	R0603	R0603/50ppm/5.1k/1%/(1/16W)	1
1.2K	0603/100ppm/1.2K/1%/(1/16W)	R21	R0603	R0603/100ppm/1.2K/1%/(1/16	1
33K	0603/100ppm/33K/1%/(1/16W)	R22	R0603	R0603/100ppm/33K/1%/(1/16	1
16K	0603/250ppm/16K/1%/(1/16W)	R30, R31	R0603	R0603/250ppm/16K/1%/(1/16	2
33R	33R/1%	R44, R45	R0603	R0603/33R/1%	2
AT24C08		U1	SOP65P640X110-8N	AT24C08	1
ADS1292R		U2	QPF50P-32	ADS1292R	1
TPS79133		U3	SOT-23-5	TPS79133	1
REF3030		U4	SOT23-3	REF3030	1
STM32F103C8	STM32F103C8 /LQFP48/ 意法半导体	U5	LQFP48	STM32F103C8	1
Mini USB		U7		Mini USB	1
12MHz/ 无源	10M/ 无源四脚	X1	Y5032	XTAL/10MHz/ 无	1