












DRV8412DDW EVALUATION BOARD

REV G



DRV8412DDW EVALUATION BOARD

REV G



REVISION HISTORY PAGE 1			
REVISION	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	APRIL 23, 2009	ML
B	PCB EDITS ONLY, NO SCHEMATIC CHANGES	MAY 13, 2009	ML
C	1. REMAPPED INPOUT CONNECTOR, J1. 2. ADDED 5V VOLTAGE REGULATOR CIRCUIT. 3. DELETED R5. R6, R8, R9, R10, R11, R12, R13 AND R14. 4. DELETED R16. 5. RENAMED AGND TO GND. (PIN 12) 6. CONNECTED PIN 12 TO GND. 7. EDITED MODE SELECTION MATRIX. 8. CHANGED C11 TO 22UFD/16V. 9. CHANGED C12 TO 1.0UFD/16V.	July 13, 2009	ML
D	1. RENUMBERED U2 TO U1. 2. RENUMBERED J6 TO J2. 3. CHANGED C4 TO FC 330UFD/16V. 4. CHANGED C11 TO FC 47UFD/16V. 5. CHANGED C12 TO 0603/0.1UFD/16V. 6. CHANGED C15/18/20/23 TO 0805/0.1UFD/100V. 7. ADD R7, 1 OHM 0805 1/4W, BETWEEN AGND AND GND.	OCTOBER 30, 2009	ML
E	1. ADDED DIMM SOCKET FOR CC8250 BOARD. 2. MOVED M1-3, M2-3, M3-3 TO AGND. 3. ADDED PVDD TO 5V SWITCHER CIRCUIT. 4. ADDED 1.25V VOLTAGE REGULATOR. (VR3) 5. CHANGED JST CONNECTORS TO BANANAS. 6. ADDED JUMPER FOR OC-ADJ. 7. ADDED ENCODER HEADERS.	DECEMBER 21, 2009	ML
F	1. MOVED RESET_AB LINE TO J1-89. 2. CHANGED R48/R49/R54/R55 TO 49.9K OHMS. 3. CHANGED R28/R29/R30/R31/R32/R33/R34/R35 TO 1.00K OHMS. 4. CONVERTED 1.25V TO 2.5V. 5. ADDED R62/R63/R64/R65 TO OA1/2 PINS 3/5. VALUE = 49.9K OMS. 6. CORRECTED PART NUMBER FOR VR1 7. CHANGED VR4 TO 2.5V VOLTAGE REFERENCE. 8. CHANGED C19/C20/C21/C22/C25/C26/C27/C28 TO DNP. 9. CHANGED C5 AND C6 TO 100V. 10. CHANGED C4 TO 22UFD/100V.	NOVEMBER 4, 2010	KM

REVISION HISTORY PAGE 2			
REVISION	DESCRIPTION	DATE	APPROVAL
G	1. CHANGED R24-R27 TO 0603-22.6K OHMS. 2. CHANGED R48, R49, R54 AND R55 TO 0603-34.0K OHMS. 3. CHANGED R56-R61 TO 0603-49.9K OHMS. 4. CHANGED R37 TO 36K OHMS.	JANUARY 26, 2011	RK

# TEXAS INSTRUMENTS DISCLAIMER

The information and materials ("Materials") provided here are provided by Texas Instruments Incorporated ("TI") as a service to its customers and/or suppliers, and may be used for informational purposes only, and only subject to the following terms. By downloading or viewing these Materials, you are signifying your assent to these terms.

1.) These preliminary evaluation schematics are intended for use for PRELIMINARY ENGINEERING DEVELOPMENT AND EVALUATION PURPOSES ONLY and are not considered by Texas Instruments to be fit as a basis for establishing production products or systems. This information may be incomplete in several respects, including but not limited to information relating to required design, marketing, and/or manufacturing-related protective considerations and product safety measures typically found in the end-product incorporating the goods.

2.) Accordingly, neither TI nor its suppliers warrant the accuracy or completeness of the information, text, graphics, links or other items contained within the Materials. TI may make changes to the Materials, or to the products described therein, at any time without notice. TI makes no commitment to update the Materials.

3.) TI assumes no liability for applications assistance, customer product design, software performance, or services that may be described or referenced in the Materials. The user assumes all responsibility and liability for proper and safe design and handling of goods. Accordingly, the user indemnifies TI from all claims arising from its use of the Materials.

4.) TI currently deals with various customers for products, and therefore our arrangement with the user will not be exclusive. TI makes no representations regarding the commercial availability of non-TI components that may be referenced in the Materials.

5.) No license is granted under any patent right or other intellectual property right of TI covering or relating to any combination, machine, or process in which such TI products or services might be or are used. Except as expressly provided herein, TI and its suppliers do not grant any express or implied right to you under any patents, copyrights, trademarks, or trade secret information.

6.) Performance tests and ratings, to the extent referenced in the Materials, are measured using specific computer systems and/or components and reflect the approximate performance of TI products as measured by those tests. Any difference in system hardware or software design or configuration may affect actual performance. Buyers should consult other sources of information to evaluate the performance of systems or components they are considering purchasing.

7.) Resale of TI's products or services with statements different from or beyond the parameters stated by TI for that product or service in official TI data books or data sheets voids all express and any implied warranties for the associated TI product or service, and is an unfair and deceptive business practice, and TI is not responsible for any such use.

8.) The Materials are copyrighted and any unauthorized use may violate copyright, trademark, and other laws. You may only download one copy for your internal use only, unless you are specifically licensed to do otherwise by TI in writing. This is a license, not a transfer of title, and is subject to the following restrictions: You may not:

- (a) modify the Materials (including any associated warranties, conditions, limitations or notices) or use them for any commercial purpose, or any public display, performance, sale or rental;
- (b) decompile, reverse engineer, or disassemble software Materials except and only to the extent permitted by applicable law;
- (c) remove any copyright or other proprietary notices from the Materials;
- (d) transfer the Materials to another person. You agree to prevent any unauthorized copying of the Materials. TI may terminate this license at any time if you are in breach of the terms of this Agreement. Upon termination, you will immediately destroy the Materials.

9.) THE MATERIALS ARE PROVIDED "AS IS" WITHOUT ANY EXPRESS OR IMPLIED WARRANTY OF ANY KIND INCLUDING WARRANTIES OF MERCHANTABILITY, NONINFRINGEMENT OF INTELLECTUAL PROPERTY, OR FITNESS FOR ANY PARTICULAR PURPOSE. IN NO EVENT SHALL TI OR ITS SUPPLIERS BE LIABLE FOR ANY DAMAGES WHATSOEVER (INCLUDING, WITHOUT LIMITATION, DAMAGES FOR LOSS OF PROFITS, BUSINESS INTERRUPTION, LOSS OF INFORMATION) ARISING OUT OF THE USE OF OR INABILITY TO USE THE MATERIALS, EVEN IF TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.