



VSYNC >> VSYNC


File	<Title>		
Size	Document Number		
C	<Doc>		
Date	Friday, May 20, 2016	Sheet	1 of 4

如果汽车电源单一，稳定，可直接给功放供电：LM25118 不贴，FB1,FB2, FB3上件；


9V TO 36V




EMI Protection




充电时间 $= 5R * 10F * 3 = R * C * 3 = 150 \text{ s}$.
 开机启动延时时间 $= 5R * 10F * \ln(5 / (5 - (0.7 + 2.7))) = 57 \text{ s}$.





282104-1




File	<Title>	Rev	<Rev Code>
Size	Document Number		
C	<Doc>		
Date	Friday, May 20, 2016	Sheet	2 of 4




+4.75 <485_VCC <+5.25V





MUTE >>> MUTE



Title		<Title>	
Size	Document Number	Rev	
B	<Doc>	<Rev Code>	
Date:	Friday, May 20, 2016	Sheet	3 of 4



PVCC_4.5V TO 26V



定位孔

File	<Title>	Rev	<Rev Code>
Size	Document Number		
C			
Date	Friday, May 20, 2016	Sheet	4 of 4