

	* SURFACE - AIR 0 MM
	L1: TOP CONDUCTOR - COPPER 0.035 MM
	* DIELECTRIC - FR-4 0.4 MM
	L2: L2 PLANE - COPPER 0.035 MM
	* DIELECTRIC - FR-4 0.66 MM
	L3: L3 PLANE - COPPER 0.035 MM
	* DIELECTRIC - FR-4 0.4 MM
	L4: BOTTOM CONDUCTOR - COPPER 0.035 MM
	* SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART
TOTAL THICKNESS 1.6 MM



DRILL CHART: TOP to BOTTOM				
ALL UNITS ARE IN MILLIMETERS				
FIGURE	FINISHED_SIZE	ROTATION	PLATED	QTY
.	0.2	-	PLATED	679
⊙	0.201	-	PLATED	28
•	1.05	-	PLATED	75
•	1.1	-	PLATED	1
⚙	3.2	-	PLATED	2
.	0.899	-	NON-PLATED	6
.	1.001	-	NON-PLATED	3
.	3.2	-	NON-PLATED	4
◊	1.3x0.6	90.000	PLATED	2