




Bridge Sensor Connector



1W Connector




Sensor Signal Conditioning



4-20mA Transmitter

Loop Connector



Texas Instruments and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. Texas Instruments and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. Texas Instruments and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Designed for: Public Release		Mod. Date: 5/14/2013	
Project Title: Change in menu Project/Project Options/Parameters		Sheet Title:	
Number: XX###	Rev: E1	Assembly Variant: Variant name not interpreted	Sheet 1 of 1
SVN Rev: Not in version control		File: PGA308_Ref_SchDoc	Size: B
Drawn By:		Engineer: Enter name of project lead	Contact: http://www.ti.com/support

<Parameter Title not found>

PGA308_Ref.PrjPCB

PGA308_Ref.PrjPCB

None

3:32:38 PM

3:32:48 PM



Description		Footprint	Quantity	Item #	Designator	Column Name Error:Manufacturer	Column Name Error:Manufacturer1	Pin Name Error:Unit	Column Name Error:Manufacturer	Column Name Error:Manufacturer2	Pin Name Error:Unit	Total Price (\$)
CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference]		0402	13		C1, C2, C3, C4, C6, C7, C8, R1, R2, R3, R4, R5, R6							0
CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], 300mA Ferrite Bead, 600 ohm @ 100MHz, 300mA Ferrite Bead, 600 ohm @ 100MHz		0603	3		C5, FB1, FB2							0
SMB			1		D1							0
PCBComponent_1			1		D2							0
SMB			1		D3							0
Header, TH, 100mil, 2x1, Gold plated, 230 mil above insulator			2		J1, J2							0
Header, TH, 100mil, 4x1, Gold plated, 230 mil above insulator			1		J3							0
Transistor, NPN, 45V, 1A, SOT-89			1		Q1							0
DG50010A_N			1		U1							0
D0008A_N			1		U2							0
											TOTAL PRICE	0.000