

QUAD-CHANNEL TIME MEASUREMENT UNIT (TMU)

Check for Samples: [THS788](#)

FEATURES

- Four Event Channels + Sync Channel
- Single-Shot Accuracy: 8 ps, One Sigma
- Precision: 13 ps (LSB)
- Result Interface Range: 0 s to 7 s
- Event Input Rate: 200 MHz
- Low TC: 0.1 ps/°C
- High-Speed Serial Host-Processor Bus Interface: 50 MHz
- Programmable Serial-Result Interface Speed: 75 MHz–300 MHz
- High-Speed LVDS-Compatible Serial-Result Bus per Channel
- Programmable Serial-Result Bus Length
- Temperature Sensor
- Single 3.3-V Supply
- Power: 675 mW/Channel, 18 Bits, 300 MHz, Four Channels

APPLICATIONS

- Automatic Test Equipment
- Benchtop Time-Measurement Equipment
- Radar and Sonar
- Medical Imaging
- Mass Spectroscopy
- Nuclear/Particle Physics
- Laser Distance Measurement
- Ultrasonic Flow Measurement

DESCRIPTION

The THS788 is a four-channel timing measurement unit (TMU) that incorporates a time-to-digital converter (TDC) architecture for fast and accurate measurements. The TMU is able to provide 8 ps of single-shot accuracy. The TDC has 13 ps resolution (LSB), which is derived from an external master clock of 200 MHz. It uses fast LVDS-compatible interfaces for all of its event inputs and serial result outputs, which allows for fast and reliable data transfer. Each channel can process time stamps at a maximum speed of 200 MSPS.

The THS788 has a wide range of programmability that makes it flexible in different applications. The serial-result interface has programmable data length, frequency, and data-rate mode (DDR and normal). The event channels can be programmed to take time stamps on rising edges or falling edges. The TMU has a mode for event management, where the user can program wait times before measurements. This programming is achieved through a 50-MHz LVCMOS interface.

The THS788 is available in a TQFP-100 with a heat slug on top for easy heat-sink access. The device is built using Texas Instruments RF SiGe process technology, which allows for maximum timing accuracy with low power.

Table 1. PACKAGE/ORDERING INFORMATION⁽¹⁾

TEMPERATURE	PACKAGE ⁽²⁾	ORDERABLE PART NUMBER		TOP-SIDE MARKING
0°C to 70°C	PFD	THS788PFD	Tray, 90	THS788PFD
		THS788PFDT	Tape and reel, 250	

(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.

(2) Package drawings, standard packaging quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

TMU BLOCK DIAGRAM



B0347-01

Figure 1. TMU Block Diagram

ABSOLUTE MAXIMUM RATINGS

over operating junction temperature range (unless otherwise noted)

		VALUE	UNIT
V_{CC}		4	V
Analog I/O to GND ⁽¹⁾		-0.3 to $V_{CC} + 0.3$	V
Digital I/O to GND		-0.3 to $V_{CC} + 0.3$	V
T_J	Maximum junction temperature ⁽²⁾	150	°C
T_{stg}	Storage temperature	150	°C
ESD ratings	HBM	2000	V
	CDM	250	

(1) LVDS outputs are not short-circuit-proof to GND.

(2) The THS788 has an automatic power shutdown at 140°C, typical.

POWER CONSUMPTION

Typical conditions are at 55°C junction temperature, $V_{CC} = 3.3$ V

CONDITION		CURRENT		UNIT
		TYP	MAX	
One channel plus sync, counter length = 18 bits, output interface speed = 75 MHz		420		mA
As above with an additional channel		add 125		mA
Output interface speed	150 MHz	add 10		mA
	300 MHz	add 25		
Counter length	27 bits	add 60		mA
	34 bits	add 105		
Four channel current	18 bits	75 MHz	795	1075
		150 MHz	805	1090
		300 MHz	820	1101
	27 bits	75 MHz	855	1150
		150 MHz	865	1165
		300 MHz	880	1176
	34 bits	75 MHz	900	1210
		150 MHz	910	1225
		300 MHz	925	1236

RECOMMENDED OPERATING CONDITIONS

over operating junction temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_{CC}	Supply voltage	3.135	3.465		V
T_J	Junction temperature	0	105		°C
	MCLOCK frequency		200		MHz

THERMAL CHARACTERISTICS

over operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$R_{\theta JP}$	Thermal resistance, junction-to-pad		3.11		°C/W

ELECTRICAL CHARACTERISTICS

Typical conditions are at $T_J = 55^\circ\text{C}$ and $\text{VCC} = 3.3 \text{ V}$.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
TDC CHARACTERISTICS					
Time-measurement precision (LSB)		13.02			ps
Measurement accuracy after calibration, mean		±8			ps
Single-event accuracy, one sigma		8			ps
Time-measurement temperature coefficient		0.1			$\text{ps}/^\circ\text{C}$
Time-measurement voltage coefficient		±30			ps/V
Event input rate		200			MHz
Minimum event pulse duration	With preconditioning	2.5			ns
	Without preconditioning	250			ps
Turnon time (ready to take timestamp)		250			μs
MASTER CLOCK CHARACTERISTICS					
Frequency		200			MHz
Duty cycle		0.4	0.6		
Jitter		3	ps rms		
HIGH-SPEED LVDS INPUTS: MCLK, Event, SYNC					
Differential input voltage	100-Ω termination, line-to-line	200	350	500	mV
Common-mode voltage		1.25			V
Peak voltage, either input		0.6	1.7		V
Input capacitance		1			pF
HIGH-SPEED LVDS OUTPUTS: Rdata, Rstrobe, RCLK					
Differential output voltage	100-Ω termination, line-to-line	250	325	400	mV
Common-mode voltage		1.125	1.28	1.375	V
Rise time/fall time	20%/80%	250			ps
Output resistance		40			Ω
TEMPERATURE SENSOR DC CHARACTERISTICS					
Output voltage	$T_J = 65^\circ\text{C}$	1.69			V
Output voltage temperature slope		5			$\text{mV}/^\circ\text{C}$
Max capacitive load		30			pF
Max resistive load		10			kΩ
OVERTEMPERRATURE ALARM DC CHARACTERISTICS					
Trip point	Active-low pulldown	141			°C
Leakage current	Temperature < trip point	1			μA
Output voltage, low	$I_{\text{sink}} = 1 \text{ mA}$	0.2			V
OUTPUT INTERFACE TIMING					
RCLK duty cycle		45%	50%	55%	
Rdata/Rstrobe to RCLK setup time	300 MHz	1.4			ns
	150 MHz	3.1			
	75 MHz	6.4			
Rdata/Rstrobe to RCLK hold time	300 MHz	1.5			ns
	150 MHz	3.2			
	75 MHz	6.5			

HOST SERIAL INTERFACE DC CHARACTERISTICS

over operating junction temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{IH} High-level input voltage		$0.7 \times VCC$		$VCC + 0.5$	V
V_{IL} Low-level input voltage		GND – 0.3		$0.3 \times VCC$	V
V_{OH} High-level output voltage		$VCC - 0.5$		$VCC + 0.3$	V
V_{OL} Low-level output voltage		0		0.4	V
I_{lkg} Leakage current				1	μA


HOST SERIAL INTERFACE AC CHARACTERISTICS

over operating junction temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
HCLK frequency				50	MHz
Rise and fall times				3.5	ns
HCLK duty cycle		40%	50%	60%	
Hstrobe high period between two consecutive transactions		40			ns
Hstrobe low to HCLK high setup		5			ns
HCLK high to Hstrobe high hold time		5			ns
Hdata in to HCLK high setup		5			ns
Hdata in to HCLK high hold time		5			ns
HCLK falling edge to Hdata out (L or H)	$C_L = 20 \text{ pF}$	3.25			ns
HCLK falling edge to Hdata out (H or L)	$C_L = 20 \text{ pF}$	3.25			ns

DEVICE INFORMATION

PIN ASSIGNMENT



P0011-03

Note: Pin 1 indicator is symbolized with a white dot, and is located near pin 1 corner.

Figure 2. Pinout Diagram

PIN FUNCTIONS

PIN		FUNCTION	DESCRIPTION
NAME	NO.		
EventA	68	LVDS-compatible input	Positive event input for channel A
EventA	66	LVDS-compatible input	Negative event input for channel A
EventB	61	LVDS-compatible input	Positive event input for channel B
EventB	63	LVDS-compatible input	Negative event input for channel B
EventC	8	LVDS-compatible input	Positive event input for channel C
EventC	10	LVDS-compatible input	Negative event input for channel C
EventD	15	LVDS-compatible input	Positive event input for channel D
EventD	13	LVDS-compatible input	Negative event input for channel D
GND	1, 2, 11, 12, 21, 25, 32, 35, 37, 39, 42, 55, 64, 65, 74, 75, 82, 84, 85, 87, 89, 92, 94	Ground	Chip ground
HCLK	34	LVCMS input	Host serial-interface clock
Hdata	33	LVCMS I/O	Host serial-interface data I/O
Hstrobe	41	LVCMS input	Host serial-interface chip select
MCLK	19	LVDS-compatible input	Positive master-clock input
MCLK	20	LVDS-compatible input	Negative master-clock input
NC	3–6, 9, 14, 17, 18, 26, 50, 54, 59, 62, 67, 70–73, 76, 100	No connect	Physically not connected to silicon
OT_ALARM	53	Open-drain output	Overtemperature alarm
RCLK	45	LVDS-compatible output	Positive result-interface clock
RCLK	44	LVDS-compatible output	Negative result-interface clock
RdataA	78	LVDS-compatible output	Positive result-data output for channel A
RdataA	79	LVDS-compatible output	Negative result-data output for channel A
RdataB	49	LVDS-compatible output	Positive result-data output for channel B
RdataB	48	LVDS-compatible output	Negative result-data output for channel B
RdataC	98	LVDS-compatible output	Positive result-data output for channel C
RdataC	97	LVDS-compatible output	Negative result-data output for channel C
RdataD	27	LVDS-compatible output	Positive result-data output for channel D
RdataD	28	LVDS-compatible output	Negative result-data output for channel D
Reserved	23, 24, 90, 91	Engineering or test pins	Connect to VCC
Reset	51	LVCMS input	Chip reset, active-low
RstrobeA	80	LVDS-compatible output	Positive strobe signal for channel A
RstrobeA	81	LVDS-compatible output	Negative strobe signal for channel A
RstrobeB	47	LVDS-compatible output	Positive strobe signal for channel B
RstrobeB	46	LVDS-compatible output	Negative strobe signal for channel B
RstrobeC	96	LVDS-compatible output	Positive strobe signal for channel C
RstrobeC	95	LVDS-compatible output	Negative strobe signal for channel C
RstrobeD	29	LVDS-compatible output	Positive strobe signal for channel D
RstrobeD	30	LVDS-compatible output	Negative strobe signal for channel D
SYNC	57	LVDS-compatible input	Positive input for sync channel
SYNC	56	LVDS-compatible input	Negative input for sync channel
TEMP	52	Analog output	Die temperature
VCC	7, 16, 22, 31, 36, 38, 40, 43, 58, 60, 69, 77, 83, 86, 88, 93, 99	Power supply	Positive supply, nominal 3.3 V

THS788 CIRCUIT FEATURES

The THS788 time-measurement unit (TMU) includes four measurement channels plus a synchronization channel optimized to make high-accuracy time-interval measurements. The following is a brief description of the various circuit blocks and how they interact to make and process the time measurements.

Counter, Latches, Clock Multiplier

The center of the TMU is a master synchronous counter which counts continuously at a rate of 1.2 GHz. This is the master timing generator for the whole TMU and defines the basic timing interval of 833 ps, which is further subdivided with Interpolator circuitry. The counter is divided into four sections, which can be powered off so that the effective length is selectable as 18, 27, or 34 bits long. The output bits of the counter are connected to five sets of latches, which can latch and hold the counter state on command from each of the channels. In this way, when an event occurs, the counter time is recorded in the particular channel's latches. The latch output is converted to CMOS levels and passed to the respective channel's FIFO buffer, which is 15 samples deep. The counter 1.2-GHz clock is derived from the MCLK input to the TMU at 200 MHz. This MCLK input is critical to the accuracy of the TMU, and any error in frequency is reflected as errors in time measurement. Likewise, jitter propagates to the counter and other circuits and adds noise to the measurement accuracy. The 200-MHz clock is the input to a clock multiplier. The clock multiplier uses delay-lock loop (DLL) techniques and combinatorial logic to construct a six-times clock from the reference input. This 1.2-GHz clock is passed to a high-power clock buffer, which drives all the circuitry in the master counter and many other circuits in the TMU.

Channels, Interpolator, Preconditioning

There are four event channels and one sync channel. The event channels are identical, and the sync channel contains most of the event channel circuitry, but without a FIFO and preconditioning. An input pulse to the sync channel serves as the reference time zero for the TMU. An event input to a channel is compared to the sync time reference, and the time delay is calculated as the time difference modified by a calibration value. An event input follows the following signal path: the event input edge sets a fast latch (hit latch). This latch is gated on/off by a block of preconditioning logic which can set up holdoff delay conditions to determine when to allow the latch to accept an event pulse. This document discusses holdoff preconditioning in more complete detail in later sections. The output of the latch is current-buffered and applied to the interpolator. The interpolator uses DLL techniques to subdivide the counter interval of 833 ps into 64 time intervals of 13 ps each. A large array of fast latches triggered by the hit latch captures the state of the 64 time intervals and logically determines 6 bits of timing data based on where the event occurred in the 833-ps clock interval. These 6 bits are latched and eventually passed to the FIFO, where they become the LSBs of the time-to-data conversion. A synchronizer circuit is also connected to the 64-latch array and removes the possible timing ambiguity between the 64 latches and the master counter. This takes a few 1.2-GHz clock pulses. When this process is complete, a pulse occurs which captures the master counter bits into the channel latches. A subsequent pulse loads all the bits from the interpolator and the counter into the channel FIFO. While this is happening, the hit latch is being reset, and the channel is prepared to accept another event edge. This process is fast enough to accept and measure event edges as close together as 5 ns.

FIFO

Each event channel contains a 15-deep, 40-bit-wide FIFO, which allows for rapid accepting and measurement of event inputs and a user-defined data-output rate of those measurements.

Calibration, ALU, Tag, Shifter

The output of the FIFO is controlled by the shifter, which is a free-running parallel-to-serial register. The shifter bit length and clock rate are user controlled. The shifter generates a load pulse, which transfers the data in the FIFO output into an arithmetic logic unit, which does the sync time and calibration time subtractions and then parallel-loads the result into the output serial register. An LVDS output buffer outputs the clock, data, and strobe signals to transfer the time-measurement data to the user. A TAG bit is appended to the leading edge of the data word. Currently the TAG feature is not implemented. The bit will always be 0 representing data.

Serial Interface, Temperature, Overhead

The TMU functions and options are controlled and read out by a serial interface built in CMOS logic that can operate up to 50 MB/s. There is one central controller which then drives registers, counters, etc., in each channel. A temperature sensor is located central to the chip and outputs a voltage proportional to the chip temperature. If the chip temperature rises above 141°C, the TMU powers down and outputs an overtemperature alarm signal. The TMU does not restart without a command through the serial interface. A bias circuit provides a regulated current bias and voltage reference for the TMU. The serial controller sequences some of the bias circuits to account for some acquisition times, and thereby, turns on the TMU.

Host Processor Bus Interface

The THS788 includes a high-speed serial interface to a host processor. The host interface is used for writing or reading registers that reside in the TMU chip. These registers allow configuration of the device functions. All registers are capable of both read and write operations unless otherwise stated.

Serial Interface

The TMU serial interface operates at speeds of up to 50 MHz. Register addresses are 8 bits long. Data words are 16 bits wide, enabling more-efficient interface transactions. The serial bus implementation uses three LVCMOS signals: HCLK, Hstrobe, and Hdata. The HCLK and Hstrobe signals are inputs only, and the Hdata signal is bidirectional. The HCLK signal is not required to run continuously. Thus, the host processor may disable the clock by setting it to a low state after the completion of any required register accesses.

When data is transferred into the device, Hdata is configured as an input bus, and data is latched on a rising edge of HCLK. When data is transferred out of the part, Hdata is configured as an output bus, and data is updated on the falling edge of HCLK. Hstrobe is the control signal that identifies the beginning of a host bus transaction. Hstrobe must remain low for the duration of the transaction, and must go high for at least two clock cycles before another transaction can begin.

Read vs Write Cycle

The first Hdata bit latched by HCLK in a transaction identifies the transaction type.

First Hdata bit = 1 for read; data flows out of the chip.

First Hdata bit = 0 for write; data flows into the chip.

Parallel (Broadcast) Write

Parallel write is a means of allowing identical data to be transferred to more than one channel in one transaction. The second Hdata bit of a transaction indicates whether a parallel write occurs.

Second Hdata bit = 0; data goes to the selected channel.

Second Hdata bit = 1; data goes to all four channels.

Address

After the R/W bit and the parallel write bit, the following 8 bits on the Hdata line contain the source address of the data word for a read cycle or the destination address of the data word for a write cycle. Address bits are shifted in MSB first, LSB last.

Third HCLK – Address Bit 7 (MSB)

Tenth HCLK – Address Bit 0 (LSB)

Data

The data stream is 16 bits long, and it is loaded or read back MSB first, LSB last. The timing for read and write cycles is different, as the drivers on Hdata alternate between going into high-impedance and driving the line.

Reset

Reset is an external hardware signal that places all internal registers and control lines into their default states. The THS788 resets after a power-up sequence (POR). Hardware reset is an LVCMOS active-low signal and is required to stay low for approximately 100 ns.

Reset places the TMU in a predetermined idle state at power on, and anytime the system software initializes the system hardware. In the idle state, the TMU ignores state changes on the Event inputs and never creates time stamps. The TMU is capable of switching within 250 μ s from the idle state to a state that creates accurate time stamps.

Chip ID

Address (83h) is a read-only register that identifies the product and the die revision. The 16-bit register is divided into two 8-bit sections. The LSB represents the revision history and the MSB represents the last two digits of THS788 (i.e., 80). The first revision (1.0) is as follows:


1000 0000 0001.0000

Read Operations

Reading the THS788 registers via the host interface requires the following sequence:

The host controller initiates a read cycle by setting the host strobe signal, Hstrobe, to a low state. The serial Hdata sequence starts with a high R/W bit, followed by (either 1 or 0) for parallel-write bit and 8 bits of address, with most-significant bit (A7) first. The host controller should put the Hdata signal in the high-impedance state beginning at the falling edge of HCLK pulse 10. The THS788 allows one clock cycle, (r) for the host to reverse the data-channel direction and begins driving the Hdata line on the falling edge of HCLK pulse 12. The data is read beginning with the most-significant bit (D15) and ending with the least-significant bit (D0).

The host must drive Hstrobe to a high state for a minimum of two HCLK periods beginning at the falling edge of HCLK pulse 27 to indicate the completion of the read cycle. [Figure 3](#) shows the timing diagram of the read operation.




T0427-01

Figure 3. Read Operation

Write Operations

Writing into the THS788 registers via the host interface requires the following sequence:

After the Hstrobe line is pulled low (start condition), the R/W bit is set low, followed by a 0 for the parallel-write bit (single-register write), then the memory address (A7–A0) followed by the data (D15:D0) to be programmed. The next clock cycle (w) is required to allow data to be latched and stored at the destination address (or addresses in the case of a parallel write), followed by at least two dummy clock cycles during which the Hstrobe is high, indicating the completion of the write cycle. [Figure 4](#) and [Figure 5](#) show timing diagrams of write operations.




T0425-01

Figure 4. Write Operation

Write Operations to Multiple Destinations

This is similar to the single-write operation except the parallel-load bit is set to 1.



T0426-01

Figure 5. Write Operations to Multiple Destinations

REGISTER ADDRESS SPACE

Table 2. Channel-A Registers

Address (Hex)	Register	
00h–01h	Control register	R/W
02h–03h	Not used	NA
04h	Status registers	RO
05h	Not used	NA
06h	Holdoff delay time register	R/W
07h	Not used	R/W
08h	Not used	R/W
09h	Not used	R/W
0Ah	Not used	R/W
0Bh	Not used	R/W
0Ch	Positive edge sync and positive edge hit calibration register, 16 bits	R/W
0Dh	Positive edge sync and negative edge hit calibration register, 16 bits	R/W
0Eh	Negative edge sync and positive edge hit calibration register, 16 bits	R/W
0Fh	Negative edge sync and negative edge hit calibration register, 16 bits	R/W
10h–12h	Time stamp register, 40 bits	R
13h–1Fh	Not used	NA

Table 3. Channel-B Registers

Address (Hex)	Register	
20h–21h	Control register	R/W
22h–23h	Not used	NA
24h	Status registers	RO
25h	Not used	NA
26h	Hold_off delay time register	R/W
27h	Not used	R/W
28h	Not used	R/W
29h	Not used	R/W
2Ah	Not used	R/W
2Bh	Not used	R/W
2Ch	Positive edge sync and positive edge hit calibration register, 16 bits	R/W
2Dh	Positive edge sync and negative edge hit calibration register, 16 bits	R/W
2Eh	Negative edge sync and positive edge hit calibration register, 16 bits	R/W
2Fh	Negative edge sync and negative edge hit calibration register, 16 bits	R/W
30h–32h	Time stamp register, 40 bits	R
33h–3Fh	Not used	NA

Table 4. Channel-C Registers

Address (Hex)	Register	
40h–41h	Control register	R/W
42h–43h	Not used	NA
44h	Status registers	RO
45h	Not used	NA
46h	Not used	R/W
47h	Not used	R/W
48h	Not used	R/W
49h	Not used	R/W
4Ah	Not used	R/W
4Bh	Not used	R/W
4Ch	Positive edge sync and positive edge hit calibration register, 16 bits	R/W
4Dh	Positive edge sync and negative edge hit Calibration register, 16 bits	R/W
4Eh	Negative edge sync and positive edge hit Calibration register, 16 bits	R/W
4Fh	Negative edge sync and negative edge hit Calibration register, 16 bits	R/W
50h–52h	Time Stamp register, 40 bits	R
53h–5Fh	Not used	NA

Table 5. Channel-D Registers

Addr (hex)	Register	
60h–61h	Control register	R/W
62h–63h	Not used	NA
64h	Status registers	RO
65h	Not used	NA
66h	Not used	R/W
67h	Not used	R/W
68h	Not used	R/W
69h	Not used	R/W
6Ah	Not used	R/W
6Bh	Not used	R/W
6Ch	Positive sync edge and positive hit edge, calibration register, 16 bits	R/W
6Dh	Positive sync edge and negative hit edge, calibration register, 16 bits	R/W
6Eh	Negative sync edge and positive hit edge, calibration register, 16 bits	R/W
6Fh	Negative sync edge and negative hit edge, calibration register, 16 bits	R/W
71h–73h	Time stamp register, 40 bits	R
74h–7Fh	Not used	NA

Table 6. Central Registers

Addr (hex)	Register	
80h	Control register	R/W
81h	Control register	R/W
82h	Status register	RO
83h	Chip ID	RO
84h	Test key register	R/W
85h	Test1	R/W
86h	Test2	R/W
87h	Reserved	R/W
88h	Reserved	R/W

REGISTER MAP DETAIL

Table 7. Channel A

Reg Addr	Reg. Name	Word/Bit												Default Value	
		15	14	13	12	11	10	9	8	7	6	5	4	3	
00h	Control	X	X	X	X	PreCon_En_A	0	0	0	0	0	0	0	0	0000h
01h	Control	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h
04h	Status	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h
06h	Hold_off delay time														0000h
0Ch	Calibration:Pos Sync EdgePos Event Edge	0	D31	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	0000h
0Dh	Calibration:Pos Sync EdgeNeg Event Edge	0	D30	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	0000h
0Eh	Calibration:Neg Sync EdgePos Event Edge	0	D29	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	0000h
0Fh	Calibration:Neg Sync EdgeNeg Event Edge	0	D28	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	0000h
10h	Time stamp	0	D27	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	0000h
11h		0	D26	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	0000h
12h		0	D25	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	0000h
		0	D24	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	0000h
		D39	D23	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	0000h
		D38	D22	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	0000h
		D37	D21	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	0000h
		D36	D20	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	0000h
		D35	D19	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	0000h
		D34	D18	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	0000h
		D33	D17	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	0000h
		D32	D16	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	0000h

Table 8. Channel B

Table 9. Channel C

Reg. Addr.	Reg. Name	Word/Bit																Default Value				
		15	14	13	PreCon_En_C	12	11	10	HOffTm_En_C	9	HOffRng2_C	8	HOffRng1_C	7	HOffRng0_C	6	5	4	3	2	1	0
40h	Control	X	X	X	PreCon_En_C	0	0	0	HOffTm_En_C	X	X	X	HOffRng1_C	0	En_ChC	0000h						
41h	Control	X	X	X	X	X	X	X	X	X	X	X	HOffRng0_C	0	0000h							
44h	Status	X	X	X	X	X	X	X	X	X	X	X	HOffRng0_C	0	0000h							
46h	Hold_Off Delay Time	0	D31	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	0000h
4Ch	Calibration:Pos Sync EdgePos Event Edge	0	D30	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	0000h
4Dh	Calibration:Pos Sync EdgeNeg Event Edge	0	D29	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	0000h
4Eh	Calibration:Neg Sync EdgePos Event Edge	0	D28	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	0000h
4Fh	Calibration:Neg Sync EdgeNeg Event Edge	0	D27	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	0000h
50h	Time Stamp	0	D26	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	0000h
51h		0	D25	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	0000h
52h		0	D24	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	0000h
		0	D39	D23	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	0000h
		0	D38	D22	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	0000h
		0	D37	D21	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	0000h
		0	D36	D20	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	0000h
		0	D35	D19	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	0000h
		0	D34	D18	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	0000h
		0	D33	D17	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	0000h
		0	D32	D16	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	0000h

Table 10. Channel D

Reg. Addr.	Reg. Name	Word/Bit																Default Value
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
60h	Control	X	X	X	PreCon_En_D	0	HOffTm_En_D	HOffRng2_D	HOffRng1_D	HOffRng0_D	0	0	0	0	0	0	0000h	
61h	Control	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h	
64h	Status	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h	
66h	Hold_Off Delay Time																0000h	
6Ch	Calibration:Pos Sync EdgePos Event Edge	0	D31	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	D15	0000h
6Dh	Calibration:Pos Sync EdgeNeg Event Edge	0	D30	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	D14	0000h
6Eh	Calibration:Neg Sync EdgePos Event Edge	0	D29	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	D13	0000h
6Fh	Calibration:Neg Sync EdgeNeg Event Edge	0	D28	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	D12	0000h
70h	Time Stamp	0	D27	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	D11	0000h
71h		0	D26	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	D10	0000h
72h		0	D25	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	D9	0000h
		0	D24	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	D8	0000h
		D39	D23	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	D7	0000h
		D38	D22	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	D6	0000h
		D37	D21	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	D5	0000h
		D36	D20	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	D4	0000h
		D35	D19	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	D3	0000h
		D34	D18	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	D2	0000h
		D33	D17	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	D1	0000h
		D32	D16	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	D0	0000h

Table 11. Central Registers

Reg. Addr.	Reg. Name	Word/Bit															Default Value	
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
80h	Control	RCLK_En	PWR_DN	Sync_IP_En	Sync_TS_Pol	RST_OT_ALM	OT_En	RCLK_sel1	RCLK_sel0	Rlength2	Rlength1	Rlength0	Connect_CD	Connect_AB	DDR_En	RESET	Test_En	0000h
81h	Control	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h	
82h	Status	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	0000h	
83h	Chip ID	ID	ID	ID	ID	ID	ID	ID	Rev	Rev	Rev	Rev	Rev	Rev	OT_ALM	CNT_Rng0	X	8010h

Table 12. Control and Status Register Descriptions for All Channels (X)

Register	Bit	Name	Function	LogicState	Description
00h 20h 40h 60h	0	En_ChX	Enable or disable channel X by powering down the channel. Time to enable a channel is 200 μ s.	0	Channel is disabled
	1	ChX_IP_EN		1	Channel is enabled
	1	ChX_IP_EN	Enables or disables the input of channel X. Events are prevented from entering a channel.	0	Input is disabled
	2	Pol_X		1	Input is enabled
	2	Pol_X	Defines the polarity of the event input X for the upcoming time stamp generation.	0	Positive edge
	3	Pol_X		1	Negative edge
	7	HOffRng0_X	Defines holdoff range for event input X.	0	Holdoff range value
	8	HOffRng1_X		1	Holdoff range value
	9	HOffRng2_X		0	Holdoff range value
	9	HOffRng2_X		1	Hold-off range value

Table 13. Control and Status Register Descriptions for All Channels (X)

Register	Bit	Name	Function	Logic State	Description
01h 21h 41h 61h	0	Reserved	Reserved	x	
	1	Arm_sel0X	Define arming conditions for channel X.	0	Arming value
				1	Arming value
	2	Arm_sel1X	Define arming conditions for channel X.	0	Arming value
				1	Arming value
	3	Arm_sel2X	Define arming conditions for channel X.	0	Arming value
				1	Arming value
	4	Arm_sel3X	Define arming conditions for channel X.	0	Arming value
				1	Arming value
	5	Armg_Con_En_X	Enables or disables the arming conditions for channel X.	0	Arming cond. disabled
				1	Arming cond. enabled
04h 24h 44h 64h	0	DLL_Lock_X	Indicates the DLL lock status for channel X.	0	DLL locked
				1	DLL not locked
	2	Reserved	Reserved	x	
	3	FIFO_Full_X	Indicates that the FIFO is full. Time stamps arriving while FIFO is full are lost.	0	FIFO not full
				1	FIFO full
04h 24h 44h 64h	4	FIFO_Empty_X	Indicates that the FIFO is empty.	0	FIFO not empty
				1	FIFO empty

Table 14. Central Control and Status Registers Description

Register	Bit	Name	Function	Logic State	Description
80h	0	TEST_En	Enables or disables factory test routines.	0	Disabled
				1	Enabled
	1	RESET	Reset the device. Device is fully operational after 250 μ s.	0	
				1	Reset
	2	DDR_En	It enables DDR mode allowing the result interface to output data on both edges.	0	Normal mode
				1	DDR Mode
	3	Connect_AB	It connects channels A and B inputs together.	0	Inputs not connected
				1	Inputs connected
	4	Connect_CD	It connects channels C and D inputs together.	0	Inputs not connected
				1	Inputs connected
	5	Rlength0	Define the result data length being used for the time stamps.	0	Length value
				1	Length value
	6	Rlength1	Define the result data length being used for the time stamps.	0	Length value
				1	Length value
	7	Rlength2	Define the result data length being used for the time stamps.	0	Length value
				1	Length value
	8	RCLK_sel0	Define RCLK frequency.	0	Frequency value
				1	Frequency value
	9	RCLK_sel1	Define RCLK frequency.	0	Frequency value
				1	Frequency value
	10	OT_En	Enables or disables the over temperature alarm circuits.	0	Disabled
				1	Enabled
	11	RST_OT_ALM	Resets the temperature alarm.	0	
				1	Reset alarm state
	12	SYNC_TS_Pol	Defines the polarity of the Sync input for the upcoming time stamp generation.	0	Positive edge
				1	Negative edge
	13	SYNC_IP_ENI	Enables or disables the sync channel	0	Sync disabled
				1	Sync enabled
	14	PWR_DN	Powers down the device	0	Powered up
				1	Powered down
81h	1	CNT_Rng0	Defines the coarse counter range	0	Range value
				1	Range value
	2	CNT_Rng1	Defines the coarse counter range	0	Range value
				1	Range value
	3	Quiet_Mod	It disables the RCLK and digital clks internal during time stamp process. Allows for only 16 time stamps.	0	Normal mode
				1	Quiet mode
82h	0	TMU_Ready	Indicates that the internal clks, coarse counter and Sync channel are operational.	0	Device is not ready
				1	Device is ready
	1	OT_ALM	Over temperature alarm. Indicates that the junction temperature is 140°C.	0	No alarm
				1	Alarm is enabled
	2	DLL_Lock_Sync	Indicates the Sync channel DLL lock status.	0	DLL is locked
				1	DLL is not locked
	3	DLL_Lock_1G2	Indicates the lock status of the 1.2GHz internal clk.	0	DLL is locked
				1	DLL is not locked

Event Latches

Each event channel and the sync channel include two event latches whose inputs are both connected to the LVDS input-buffer output. One latch is the time-measurement signal path and connects to the interpolator and synchronizer. The other latch connects to the preconditioning circuitry. A selectable rising or falling edge of an event pulse sets the latch. The latch remains set until the interpolator has finished processing the event, at which time the interpolator resets the latch. The latch, however, does not accept another event pulse until the event input returns to its initial state and remains for the initial event-pulse duration. Any event transitions which occur before the interpolator has completed processing the previous event are ignored. For example, assume that *rising edge* is selected. Two rising edges can occur as quickly as 5 ns apart. The falling edge can occur anywhere from 250 ps after the rising edge to 250 ps before the next rising edge. Any other edges or glitches are ignored. In addition to the rising/falling-edge selection, the event latch includes the *gating* function whereby the preconditioning logic controls whether the TMU accepts and processes an event input. The second event latch operates similarly to the main signal-path latch with the following exceptions: The latch is followed by an ECL-to-CMOS converter, because all the preconditioning logic is CMOS instead of the fast ECL circuitry in the measurement chain. The preconditioning logic rather than the interpolator resets this latch, and the timing of the reset pulse is slightly faster than the interpolator.

Preconditioning Holdoff Delay Time

The preconditioning circuitry controls the ON/OFF state of the event latches. Following a Sync input signal, the TMU checks for a number of conditions before it proceeds with the time-measurement operation. Event input signals are ignored until all arming conditions are met. These conditions are as follows:

The hold-off delay is a programmable delay used to inhibit the creation of the next time stamp until the hold-off delay has expired. A 16-bit register is used for the hold-off delay count register. One holdoff delay register exists for each of the four event input channels.

The generation of a time stamp reloads the value from the holdoff delay register into a down counting counter. Time stamp generation pauses until hold-off delay counter reaches zero. There are seven ranges for the holdoff delay maximum duration. Three register bits are used to specify the required range.

The following table defines these ranges:

Table 15. Preconditioning Holdoff Delay Time

Range	HOffRng2_x	HOffRng1_x	HOffRng0_x	Full Range (ms)	LSB (ns)
1	0	0	0	0.655	10
2	0	0	1	2.621	40
3	0	1	0	10.486	160
4	0	1	1	41.943	640
5	1	0	0	167.772	2560
6	1	0	1	671.089	10,240
7	1	1	X	2,684	40,960

In range 1 each count in the holdoff register delays the next possible time stamps by 10 ns (100-MHz clock period). The maximum delay range for this feature is 2.684 s for each channel. To disable this feature, a register bit (HOffTm_EN_x) is set to 0.

Arming Conditions

An additional arming condition for each event channel is based on other channels meeting some preprogrammed conditions before it can become fully armed. These conditions are in addition to the individual channel arming conditions.

- A given channel does not become fully armed until one, two, or all three of the other channels are armed. A logical AND of one or more channels.
- A given channel does not become fully armed until the holdoff delay expires, the arming counter reaches zero, and the logical OR of one or more channels has been active.

The following tables define this conditional operation.

Table 16. Channel-A Conditional Arming Definition

Arm_sel3A	Arm_sel2A	Arm_sel1A	Arm_sel0A	Outcome
0	0	0	0	ChA is armed if ChB is fully armed.
0	0	0	1	ChA is armed if ChC is fully armed.
0	0	1	0	ChA is armed if ChD is fully armed.
0	0	1	1	ChA is armed if ChB AND ChC are fully armed.
0	1	0	0	ChA is armed if ChB AND ChD are fully armed.
0	1	0	1	ChA is armed if ChC AND ChD are fully armed.
0	1	1	0	ChA is armed if ChB AND ChC AND ChD are fully armed.
0	1	1	1	ChA will be armed if ChB OR ChC is fully armed.
1	0	0	0	ChA will be armed if ChB OR ChD is fully armed.
1	0	0	1	ChA will be armed if ChC OR ChD is fully armed.
1	0	1	0	ChA will be armed if ChB OR ChC OR ChD is fully armed.
1	0	1	1	Reserved
1	1	0	0	Reserved
1	1	0	1	Reserved
1	1	1	0	Reserved
1	1	1	1	Reserved

Table 17. Channel-B Conditional Arming Definition

Arm_sel3A	Arm_sel2A	Arm_sel1A	Arm_sel0A	Outcome
0	0	0	0	ChB is armed if ChA is fully armed.
0	0	0	1	ChB is armed if ChC is fully armed.
0	0	1	0	ChB is armed if ChD is fully armed.
0	0	1	1	ChB is armed if ChA AND ChC are fully armed.
0	1	0	0	ChB is armed if ChA AND ChD are fully armed.
0	1	0	1	ChB is armed if ChC AND ChD are fully armed.
0	1	1	0	ChB is armed if ChA AND ChC AND ChD are fully armed.
0	1	1	1	ChB will be armed if ChA OR ChC is fully armed.
1	0	0	0	ChB will be armed if ChA OR ChD is fully armed.
1	0	0	1	ChB will be armed if ChC OR ChD is fully armed.
1	0	1	0	ChB will be armed if ChA OR ChC OR ChD is fully armed.
1	0	1	1	Reserved
1	1	0	0	Reserved
1	1	0	1	Reserved
1	1	1	0	Reserved
1	1	1	1	Reserved

Table 18. Channel-C Conditional Arming Definition

Arm_sel3A	Arm_sel2A	Arm_sel1A	Arm_sel0A	Outcome
0	0	0	0	ChC is armed if ChA is fully armed.
0	0	0	1	ChC is armed if ChB is fully armed.
0	0	1	0	ChC is armed if ChD is fully armed.
0	0	1	1	ChC is armed if ChA AND ChB are fully armed.
0	1	0	0	ChC is armed if ChB AND ChD are fully armed.
0	1	0	1	ChC is armed if ChA AND ChD are fully armed.
0	1	1	0	ChC is armed if ChA AND ChB AND ChD are fully armed.
0	1	1	1	ChC will be armed if ChA OR ChB is fully armed.
1	0	0	0	ChC will be armed if ChB OR ChD is fully armed.

Table 18. Channel-C Conditional Arming Definition (continued)

Arm_sel3A	Arm_sel2A	Arm_sel1A	Arm_sel0A	Outcome
1	0	0	1	ChC will be armed if ChB OR ChD is fully armed.
1	0	1	0	ChC will be armed if ChA OR ChB OR ChD is fully armed.
1	0	1	1	Reserved
1	1	0	0	Reserved
1	1	0	1	Reserved
1	1	1	0	Reserved
1	1	1	1	Reserved

Table 19. Channel-D Conditional Arming Definition

Arm_sel3A	Arm_sel2A	Arm_sel1A	Arm_sel0A	Outcome
0	0	0	0	ChD is armed if ChA is fully armed.
0	0	0	1	ChD is armed if ChB is fully armed.
0	0	1	0	ChD is armed if ChC is fully armed.
0	0	1	1	ChD is armed if ChA AND ChB are fully armed.
0	1	0	0	ChD is armed if ChA AND ChC are fully armed.
0	1	0	1	ChD is armed if ChB AND ChC are fully armed.
0	1	1	0	ChD is armed if ChA AND ChB AND ChC are fully armed.
0	1	1	1	ChD will be armed if ChA OR ChB is fully armed.
1	0	0	0	ChD will be armed if ChB OR ChC is fully armed.
1	0	0	1	ChD will be armed if ChB OR ChC is fully armed.
1	0	1	0	ChD will be armed if ChA OR ChB OR ChC is fully armed.
1	0	1	1	Reserved
1	1	0	0	Reserved
1	1	0	1	Reserved
1	1	1	0	Reserved
1	1	1	1	Reserved

NOTE

When programming individual-channel arming conditions, it is important to avoid conditions where dependency would cause a lockup situation.

Additional Features

FIFO

Time stamps are written to a FIFO at high speed and read for further processing at a lower speed before being sent to the result interface. This FIFO is 15 bits deep and 40 bits wide. There are four FIFOs in THS788, one for each channel. There are two status registers (FIFO_Full_x and FIFO_Empty_x), which are set when a FIFO reaches its full capacity and when it is empty, respectively.

Serial-Results Interface and ALU

Time stamps are taken and loaded into the FIFO as events occur. Time stamps are mathematically processed by an arithmetic logic unit (ALU) which calculates the difference between the event and the sync time stamps and factors in the appropriate calibration value from the calibration register. The ALU operates on the data as it is read out of the FIFO and sent out through the serial-results interface. The serial-results interface controls the output of the FIFO. The serial-results interface is programmable in output bit rate and length.

Serial-Results Interface

The TMU captures time-stamp results and sends them to external logic using an LVDS serial-results port. The serial-results port consists of a clock signal (RCLK), four strobe signals (Rstrobex) and four data signals (Rdatax). The Rstrobex signal indicates that a time-stamp data transfer is about to begin for the corresponding channel.

The serial-result interface can be programmed to have a variable data-length format. Three register bits (Rlength0, Rlength1, and Rlength2), are used to program the required data transfer formats.

The default length of the data field is 40 bits, and it is in 2s-complement format. The following table defines the various data formats:

Table 20. Result Transfer Format and Time Range


RESULT TRANSFER FORMAT	TIME RANGE	Rlength2	Rlength1	Rlength0
8 bits	-1.653 ns to 1.667 ns	0	0	0
16 bits	-426.626 ns to 426.639 ns	0	0	1
24 bits	-109.22 μ s to 109.22 μ s	0	1	0
32 bits	-27.96 ms to 27.96 ms	0	1	1
40 bits	-7.158 s to 7.158 s	1	0	0

Note that the previous table refers to the 2s-complement format. Therefore, the 8-bit result represents a number between -127 and 128.

Result-Interface Operation


The TMU initiates a read cycle by setting the strobe signal, Rstrobe, to a low state, indicating that the data transfer is about to begin. The serial Rdata sequence starts with a TAG bit, followed by the 40-bit data (R0 to R39). R39 (MSB) is the sign bit. Following the last data bit (R39), the strobe signal (Rstrobe) goes high for two clock cycles, indicating the end of the transaction.

The data is clocked out of the TMU on the rising edge of RCLK. The receiving device clocks the data in on the rising edge of RCLK. [Figure 6](#) shows a 40-bit result on the result interface. [Figure 7](#) shows a 16-bit result on the result interface.



T0428-01

Figure 6. Result-Interface Operation A


Figure 7. Result-Interface Operation B

Note: In the preceding diagrams, only RCLK_P is drawn in order to indicate the correct edge with respect to data.

DDR Mode

The result interface may be operated using one-half the clock frequency while keeping the data bit rate unchanged. In this mode, data is clocked out of the device using both edges of RCLK. A register bit (DDR_EN) is used to enable DDR mode.

Result-Interface Clock

The result-interface clock (RCLK) is generated internally and runs at a maximum frequency of 300 MHz. RCLK is programmable and may be programmed using two register bits (RCLK_sel0 and RCLK_sel1) according to the following table:

Table 21. Result-Interface Clock

RCLK Frequency (MHz) Normal Mode	RCLK Frequency (MHz) DDR Mode	RCLK_sel1	RCLK_sel0
75 (default)	37.5	0	0
150	75	0	1
300	150	1	0

Output Interface Throughput

Multiple data-word lengths and bit speeds, combined with a 15-sample-deep FIFO, give exceptional flexibility to output data throughput. The actual throughput is easily calculated, keeping in mind the following: The selected word length includes $N - 1$ data bits and 1 sign bit, which are sent out last as the MSB. Two bit times do not have meaningful data during the Rstrobe high time. The TAG bit is appended to the data bits and is sent first. Example: for a bit rate of 300 MB/s and 16-bit length, the bit time is 3.33 ns, and the total word length is $16 + 1 + 2 = 19$ bit times. Therefore, the throughput is 15.8 M samples/s. This is a constant output sample rate. The TMU can take time measurements at up to 200 MS/s. The 15-deep FIFO buffers these two rates until it is filled, in which case samples are lost.

Serial Results Latency

The event stored in the FIFO will be transferred to ALU and subsequently to the free running results data shift register when the shift register enters a load pulse. The load pulse is generated once per ALU/shift register processing cycle. The load pulse will trigger the ALU and transfer result to the parallel to serial shift register for output. The cycle time of the load pulse is dependent upon the depth of the result transfer register and data rate. Since the results parallel to serial register is free running, the load pulse will be asynchronous to the actual event. So, the latency will depend upon where in the current cycle the load pulse occurred relative to the event being captured into the FIFO.

The worst case for data to be output from serial bus:

$$T_{\text{event}} + 5(R_{\text{clkcycles}}) + (R_{\text{datalength}} + 3) \times R_{\text{clkcycles}} + (R_{\text{datalength}} + 3) \times R_{\text{clkcycles}} \quad (1)$$

The best case for data to be output from serial bus:

$$T_{\text{event}} + 5(R_{\text{clkcycles}}) + (R_{\text{datalength}} + 3) \times R_{\text{clkcycles}} \quad (2)$$

Where:

$T_{\text{event}} = 5 \text{ ns}$ (minimum repeat capture time)

$5(R_{\text{clkcycles}})$ = number cycles for FIFO to ALU to Shift register

$R_{\text{clkcycles}}$ is period of R_{CLK} data; i.e. 300 Mhz, SDR = 3.33 ns

$R_{\text{datalength}}$ = number of results bits

In the case where $R_{\text{CLK}} = 300 \text{ MHz}$, with 16-bit serial result:

$$\text{Min Latency} = 5 \text{ ns} + 17 \text{ ns} + (16 + 3) \times 3.33 \text{ ns} = 85 \text{ ns} \quad (3)$$

$$\text{Max Latency} = 5 \text{ ns} + 17 \text{ ns} + (16 + 3) \times 3.33 \text{ ns} + (16 + 3) \times 3.33 \text{ ns} = 149 \text{ ns} \quad (4)$$

NOTE

The THS788 was intended for sync-event, event, event, sync-event ... processing. However, some applications desire the use of a sync pulse that is a fixed period. During a sync period, there could be multiple events, or no events. The TMU can be used effectively for this scenario as well.

For applications using the THS788 in this fashion, it is important to consider the uncertainty that is introduced by the load pulse timing. Since the load pulse is free running and asynchronous to any events, the latency will vary based on this timing. Additionally, the load pulse is the mechanism that will cause the ALU to grab the current sync value for the result calculation.

If an event is in the FIFO, waiting for the load pulse and a new sync occurs, the ALU will use the new sync value for calculating the result. In this case, the event would precede the sync resulting in a negative result. The system could then offset the result by one sync cycle as the result is negative, indicating that it was captured during a prior sync cycle.

TMU Calibration

The TMU calibration process is identical to a normal TMU time-stamp measurement. The process involves measuring a known interval and calculating the difference between the measured value and the actual value. The result is then stored into calibration registers inside the TMU. The TMU takes the stored calibration values and corrects the subsequent time-stamp measurements.

There are four calibration registers for each channel. These are identified as follows:

- A calibration register for positive sync edge and positive event edge
- A calibration register for positive sync edge and negative event edge
- A calibration register for negative sync edge and positive event edge
- A calibration register for negative sync edge and negative event edge

Calibration due to temperature changes following the initial system calibration may be required if temperature variations are significant.

Temperature Sensor

A temperature sensor has been located centrally in the THS788 device for monitoring the die temperature. There are two monitor outputs for this feature. An analog voltage proportional to the die temperature is presented at the TEMP pin. Also, an overtemperature alarm output is available at the OT_ALARM pin. The overtemperature alarm (OT_ALARM) is an open-drain output that is activated when the die temperature reaches 141°C.

The overtemperature alarm sets a register bit (OT_ALM) in the central register and may be accessed through the serial interface.

The overtemperature alarm initiates an automatic power down to prevent overheating of the device. The digital blocks remain functional when in automatic power down. Following a power down, the user is required to reset OT_ALM using the serial interface. A register bit (RST_OT_ALM) is used for this purpose.

The temperature-monitoring function and its associated overtemperature alarm circuit may be disabled by the user, using a register bit (OT_EN). The default for the temperature-monitoring function is enabled.

OT_EN = 1: Temperature-monitoring function is enabled.

OT_EN = 0: Temperature-monitoring function is disabled.

Counter Range

The course counter has three supported ranges: 18, 27 and 34 bits. The course counter applies to the 1.2-GHz clock.

Table 22. Counter Range

COUNTER RANGE	MAX TIME RANGE	CNT_RNG1	CNT_RNG0
Reserved	X	0	0
18 bit	218.45 μ s	0	1
27 bit	111.84 ms	1	0
34 bit	14.31 s	1	1

APPLICATION INFORMATION

BASIC THEORY OF OPERATION

The THS788 is a high-speed, high-resolution time-measurement unit that measures the difference in time between a signal applied to an event channel and the signal applied to the sync channel. This difference is then transmitted to a result interface in the form of a digital word. [Figure 8](#) shows an example of three time measurements.




Figure 8. Time-Measurement Example—With 8-Bit Words Triggered by Rising Edges

The previous time difference is calculated by an internal ALU that subtracts the time stamps created by the Event signal and the SYNC signal stored in a FIFO. These time stamps are performed by the TDC that is composed by the following: an interpolator, a synchronizer, a programmable (18-, 27-, 34-bit) counter, and a 1.2-GHz clock. It is important to note that the event and sync channels share the same TDC. When a valid edge is applied to the event channel, the TDC uses the value in the counter and stores it in the FIFO. Then the ALU uses the value of the event and the value of the sync, stored in the FIFO already, and subtracts them. After the operation is done, the final value is shifted out to the result interface for retrieval.

All the programming to the THS788 is achieved through an LVCMOS host-serial interface. With this interface, the user has the ability to set up the THS788 for time measurements. It also provides the user with different modes to retrieve the results.


Results are available through an LVDS-compatible high-speed serial interface. Data-word length and speed are programmable to cover a wide range of data rates. Each channel has its own output to maximize data throughput. All of the data ports (RdataA, -B, -C, and -D) are synchronized to a global clock.

LVDS-COMPATIBLE I/Os

The Event, SYNC, and master-clock inputs are LVDS-compatible input receivers optimized for high-speed and low-time-distortion operation. The Rdata, Rstrobe, and RCLK outputs are similarly LVDS-compatible output drivers optimized for high-speed/low-distortion operation, driving 50- Ω transmission lines. Typically, LVDS data transmission is thought of in terms of 100- Ω twisted-wire-pair (TWP) transmission lines. TWP is not applicable to printed wiring boards and high-speed operation. Therefore, the THS788 interfaces were designed to operate most effectively with 50- Ω , single-ended transmission lines. Instead of a current-mode output with its correspondingly high output impedance, a more-nearly impedance-matched voltage-mode output driver is used. This minimizes reflections from mismatched transmission line terminations and the resulting waveform distortion. The input receivers do not include the 100- Ω terminating resistor, which must be connected externally to the THS788. This was done to accommodate daisy-chaining the THS788 inputs. Input offset voltage was minimized, and the fail-safe feature in the LVDS standard was eliminated in order to minimize distortion.

LVDS-COMPATIBLE INPUTS

The four event inputs, the sync input and the master-clock input all use the same input interface circuitry. [Figure 9](#) is a simplified schematic diagram of the LVDS-compatible receiver input stage. The input signal is impedance-transformed and level-shifted with a PNP emitter-follower and translated into ECL-like differential signals with a common-emitter amplifier. There is no internal termination resistor and no internal pullup/pulldown resistors. Unused inputs may be tied off by connecting both input terminals to ground. If the input terminals are left floating, they are protected by ESD clamps from damage; however, noise may be injected into the THS788 and may degrade accuracy. The peak input voltage limits are 0.6 V to 1.7 V. Outside of these limiting voltages, parts of the input circuit may saturate and distort the timing.



S0389-01

Figure 9. Simplified Schematic of the LVDS Input

Figure 10 shows the typical input connections. The transmission line lengths must be matched from the driver to the THS788 input [<0.5 inch (1.27 cm) difference] and terminated in a $100\text{-}\Omega$ resistor placed close [<0.25 inch (0.635 cm)] to the TMU input pins. The resistor total tolerance should be below 5%. The power dissipation is below 5 mW, so small surface-mounted resistors are preferred.





Figure 10. Typical Input Connection to the THS788


LVDS-COMPATIBLE OUTPUTS

Figure 11 shows a typical wiring diagram of an LVDS output. The transmission line lengths must be matched. A termination resistor may be required if the chosen receiver does not have an internal resistor. Concerning termination resistors: LVDS was originally conceived with twisted-wire pairs of approximately $100\ \Omega$ line-to-line impedance. The $100\ \Omega$ resistor between lines is simple and effective to terminate such a line. For the higher-speed operation of the THS788, use a pair of $50\ \Omega$ transmission lines, such as microstrip on the PC board. The same $100\ \Omega$ resistor line-to-line termination works well, because the line signals are equal and opposite in phase. This results in the center of the $100\ \Omega$ resistor having a constant voltage equal to the common-mode voltage and each side having an apparent $50\ \Omega$ termination. An improvement in the termination can be achieved by splitting the $100\ \Omega$ into two $50\ \Omega$ resistors and ac-grounding (bypassing) the center to ground with a 1000-pF (not critical) capacitor. The termination improvement is usually small and increases the room and parts count. It is the best approach as long as the PCB layout high-frequency performance is not compromised by the higher parts count. As mentioned previously, the driver is optimized to drive $50\ \Omega$ transmission lines and provides a driving-point impedance approximating $50\ \Omega$ to suppress reflections. Figure 13 is a simplified schematic of the output driver. A standard ECL-like circuit drives the outputs through $25\ \Omega$ resistors. The combination of the resistors and the emitter-follower output impedance approximates $50\ \Omega$. The output emitter-followers are biased by current sources which are switched to conserve power. A feedback loop varies the voltage on the two RLs to set and maintain the 1.28-V common-mode voltage of the LVDS-compatible outputs. Another feedback loop holds the emitters of the current switches to 0.4 V to keep the 4-mA current source from saturation.

The outputs are short-circuit-proof to a 3.3-V power supply. Shorts to ground should be avoided, as the power dissipation in certain components may exceed safe limits.



S0391-01

Figure 11. Typical Output Connection to the THS788


S0392-01

Figure 12. Simplified Schematic of the LVDS Output Driver

TIME MEASUREMENT

Time measurements in the THS788 follow the timing of [Figure 13](#). This diagram illustrates that time measurements are valid as long as events do not happen at speeds higher than 200 MHz. If an event happens at less than 5 ns from the previous one, then this event is ignored. The same applies to the SYNC signal. Even though the minimum period is 5 ns, the pulse duration of both Event and SYNC signals can be as low as 200 ps.





Figure 13. Time-Measurement Example at Maximum Retrigger Rate and Minimum Pulse Duration

The TH788 is capable of making time measurements using any combination of rising-falling edge between Event and SYNC. The example in [Figure 13](#) uses rising edges only to trigger the time measurement. [Table 23](#) describes what registers bits must be programmed to achieve the desired combination. Registers to be programmed are 00h, 20h, 40h, and 60h for event channels and 80h for the sync channel. The examples in [Figure 14](#) illustrate the other three combinations. It is worth noting that all the channels can be programmed individually with respect to the sync channel.

Table 23. Trigger Polarity Programmability

Register Bits		Trigger Polarity from Sync to Event
SYNC_TS_Pol	Pol_X	
0	0	Pos to Pos
0	1	Pos to Neg
1	0	Neg to Pos
1	1	Neg to Neg



T0431-01

Figure 14. Time Measurement Examples With Different Edge Polarities

Output Clock to Data/Strobe Phasing

The output of each channel is an Rdata and Rstrobe signal. The RCLK for all the channels is a common output. At the higher output clock rates, these signals must be handled carefully. Particularly important are the termination and phase alignment of the signals at the receiving circuitry. Termination has been discussed previously. Phase alignment is now discussed: The two outputs from each channel are clocked out through identical flip-flops with the same internal clock. Data and strobe output edges from a particular channel match well (< 50 pS). The match channel-to-channel is not as good due to the greater wiring distances internal to the TMU. However, the total time difference is below 125 pS. Because the RClock is a common output, the wiring lengths from the four channels must be matched and controlled to achieve good setup and hold times at the input to the receiving circuit. The RClock rising edge is adjusted internal to the TMU to be close to the center of the eye diagram of the data/strobe signals. This is true for all four output frequencies. (The internal clock has a good 50/50 duty cycle. The rising edge clocks out the data/strobe. The falling edge is inverted and used as the RClock after appropriate adjustments for the internal propagation delay times.) The DDR clock is similarly adjusted in time to put both edges close to the center of the data/strobe outputs. The receiving circuitry requirements for setup and hold timing must be carefully examined for the proper timing. Delays may be added to the PCB microstrips to adjust timing. A good rule is 125 ps of delay per inch of microstrip length.

Master Clock Input and Clock Multiplier

All of the internal timing of the TMU is derived from the 200-MHz master clock. Therefore, its quality is critical to the accurate operation of the TMU. Absolute accuracy of the master clock linearly affects the accuracy of the measurements. This imposes little burden upon the master clock, as accurate oscillators are easy to procure or distribute. However, the jitter of the master clock is also highly critical to the single-event precision of the TMU and should be absolutely minimized (<3 ps rms). A carefully selected crystal oscillator can meet this requirement. However, jitter can build up quite quickly in a clock distribution scheme and must be carefully controlled. Be careful that the LVDS input to the master clock is not badly distorted or that the rise/fall times are slow (>.6 ns). Discussion of the clock multiplier follows: The TMU operates from a master-clock frequency of 1200 MHz, which implies a measurement period of 0.833 ns. The master counter runs from this frequency, and all the other clocks are divided down from this main clock. An interpolator allows finer precision in time measurement, as discussed

elsewhere. The clock multiplier is the circuit that takes the 200-MHz master-clock reference and generates from that the high quality 1200-MHz clock. The clock multiplier consists of five major sections: First is the delay-lock loop (DLL), which is a series connection of 12 identical and closely matched variable time-delay circuits. A single control voltage connects to each of the delay elements. The master 200-MHz clock connects to the input of the DLL. Because the period of 200 MHz is 5 ns, if the control voltage is adjusted to make the time delay of the DLL equal to 5 ns, the input and the output of the delay line is exactly phase matched. A phase detector connected to the input and the output of the delay line can sense this condition accurately, and a feedback loop with a low-offset-error amplifier is included in the clock multiplier to achieve this result. These are the second and third circuit blocks. With 12 equally spaced 200-MHz clock phases, select out six equally spaced 833-ps-wide pulses with AND gates and combine these pulses into a single 1200-MHz clock waveform with a six-input OR gate. The last circuit element is a powerful differential signal buffer to distribute the 1200-MHz clock to the various circuit elements in the TMU. The DLL feedback loop is fairly narrowband, so some time is required to allow the DLL to initialize at start-up (about 100 μ s, typical). The DLL is insensitive to the duty cycle of the input 200-MHz clock. Duty cycles of 40/60 to 60/40 are acceptable. What matters most is as little jitter as possible. See [Figure 16](#) for typical sigmas across the 200-MHz master clock 5-ns window. Data in figure represents asynchronous master clock and sync/events. Sigmas vary across the window primarily based on probabilities of one or both of the sync/events being impacted from 200-MHz switching noise.

**Figure 15. Typical per Channel Sigmas
vs
5-ns (200-MHz) Window**




Figure 16.

Temperature Measurement and Alarm Circuit

Chip temperature of the TMU is monitored by a temperature sensor located near the center of the chip. A small buffer outputs a voltage proportional to the absolute temperature of the TMU. The buffer drives a load of up to 100 pF typical (50 pF minimum) and open circuit to 10 k Ω to ground resistive. The output voltage slope is 5 mV, typical. Therefore, the output voltage equation is as follows:

$$\text{Output Voltage} = (\text{Temperature in degrees C} \times 5 \text{ mV}) + 1.365 \text{ V} \quad (5)$$

Also included in the TMU is an overtemperature comparator. At approximately 140°C, the alarm goes active, and at approximately 7°C below this temperature, the alarm becomes inactive (hysteresis of 7°C prevents tripping on noise and comparator oscillations). If the alarm goes active, the chip powers down and sets a bit in the serial register.


An alarm output pin is provided that is an open-drain output. Connect this output through a pullup resistor to the 3.3-V power supply. The resistor must be at least 3.3 k Ω . This creates a slow-speed, low-voltage CMOS digital output with a logical 1 being the normal operating state and a logical 0 being the overtemperature state.

Power Supply and Bypassing

All the high-speed time-measurement circuitry in the TMU is implemented in differential emitter-coupled logic (ECL). Besides high speed, a characteristic of differential ECL is good rejection of power-supply noise and variation. However, there is a great deal of CMOS logic, FIFO and output-serial interface circuitry that is an excellent source of power-supply current noise. Therefore, to maintain the best accuracy, the TMU power supply must be low-impedance. This is accomplished in the usual ways by careful layout, good ground and power planes, short traces to the power and ground pins, and capacitive bypassing. Recommended is a quality, low-inductance, high-frequency bypass capacitor close to each power pin of approximately 0.01 μ F. The 0402 size works well. Additional bypass capacitors of larger value should be placed near the TMU, making low-inductance connection with the power and ground planes. With a typical power-supply sensitivity of 30 ps/V, a 1% power supply shift yields a 1-picosecond additional error, making power-supply regulation important for the best accuracy.

Thermal Considerations

The TMU package provides a thermally conductive heat slug at the top for connection to an additional heatsink. The TMU can be placed into many different modes for optimization of performance vs power dissipation, and a table has been provided to help determine the power required. The heat sink should be carefully considered in order to keep the TMU temperature within required limits and to promote the best temperature stability. The TMU time measurement drift with temperature is an excellent 0.1 ps/ $^{\circ}$ C. A good heat sink design takes advantage of the low temperature drift of the TMU.



B0387-01

Figure 17. Example of Application Diagram in ATE Environment

PACKAGING INFORMATION

Orderable Device	Status ⁽¹⁾	Package Type	Package Drawing	Pins	Package Qty	Eco Plan ⁽²⁾	Lead/Ball Finish	MSL Peak Temp ⁽³⁾	Samples (Requires Login)
THS788PFD	ACTIVE	HTQFP	PFD	100	90	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-4-220C-72 HR	
THS788PFDT	ACTIVE	HTQFP	PFD	100	250	Green (RoHS & no Sb/Br)	CU NIPDAU	Level-4-220C-72 HR	

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBsolete: TI has discontinued the production of the device.

⁽²⁾ Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.




Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

⁽³⁾ MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION
REEL DIMENSIONS

TAPE DIMENSIONS


A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

TAPE AND REEL INFORMATION

*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
THS788PFDT	HTQFP	PFD	100	250	330.0	24.4	16.6	16.6	2.0	20.0	24.0	Q2

TAPE AND REEL BOX DIMENSIONS

*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
THS788PFDT	HTQFP	PFD	100	250	367.0	367.0	45.0

PFD (S-PQFP-G100) PowerPAD™ PLASTIC QUAD FLATPACK (DIE DOWN)



4146930/C 10/08

NOTES:

- All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
- This drawing is subject to change without notice.

C. Body dimensions do not include mold flash or protrusion

 D. This package is designed to be attached directly to an external heatsink. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 for information regarding recommended board layout. This document is available at www.ti.com <<http://www.ti.com>>. See the product data sheet for details regarding the exposed thermal pad dimensions.

E. Falls within JEDEC MS-026

PowerPAD is a trademark of Texas Instruments.

THERMAL PAD MECHANICAL DATA

PFD (S-PQFP-G100)


PowerPAD™ PLASTIC QUAD FLATPACK

THERMAL INFORMATION

This PowerPAD™ package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the PowerPAD package and how to take advantage of its heat dissipating abilities, refer to Technical Brief, PowerPAD Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD Made Easy, Texas Instruments Literature No. SLMA004. Both documents are available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Exposed Thermal Pad Dimensions

4211595/A 03/11


NOTE: A. All linear dimensions are in millimeters

 Tie strap features may not be present.

PowerPAD is a trademark of Texas Instruments

PFD (S-PQFP-G100)

PowerPAD™ PLASTIC QUAD FLATPACK



PowerPAD is a trademark of Texas Instruments

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46C and to discontinue any product or service per JESD48B. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components which meet ISO/TS16949 requirements, mainly for automotive use. Components which have not been so designated are neither designed nor intended for automotive use; and TI will not be responsible for any failure of such components to meet such requirements.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2012, Texas Instruments Incorporated