

Signal Chain

Texas Instruments
2013

Home



EE



Signal
Chain



Power



Technology



Locations



WeBench



Investments




Org Chart



 TEXAS
INSTRUMENTS

with our complete solutions across the board



Amplifier at a glance...

#1 in amplifier market share with 23.8%

Low Power

INA333
*Lowest Input Bias
Zero Drift In-Amp*
0.2nA I_b, 75µA
LPV521

Industry's lowest power
RRIO Op-Amp

OPA2835
*Lowest Power >50MHz
Bandwidth VFB Amp*
250µA, 59MHz GBW
OPA333

*Lowest Power
Zero Drift Op Amp*
25µA, RFI filtering
OPA378

*Lowest Noise/Power
Zero-Drift Op Amp*
20nV/rtHz, 100µA

Precision Input

INA282
*Highest Accuracy / High Voltage
Current Shunt*
-14V to 80V, 20µV Offset
LME49990
Ultra low-distortion
0.00001% THD+N @ 110MHz

OPA140
High Precision 11MHz JFET
120uVV_{os}, 1µV/°C drift,
11MHz GBW
OPA211
Lowest Noise Bipolar Amp
1.1nV/rtHz, 36V

LMP7721
*Industry's lowest
bias current*
(3 fA) Amplifier

OPA320
1pA Ibias Precision Amplifier
for Sensor Signal Conditioning
(20MHz, 1.8-5.5V)

Wide Bandwidth

LMH6554
*Ultra Linear Differential
ADC Driver*
2.8 GHz BW, flat to 830 MHz
LMH6629
*Highest Performance
Low-Noise*
Op-Amp : 0.69nV/rtHz, 900 MHz BW
OPA2673

*Dual Wideband High
Output Current*
Slew Rate: 3000 V/µs
BW: 340MHz

OPA365
*Widest GBW RRIO
Zero-Crossover CMOS Op Amp*
50MHz, 16-Bit Performance
THS4521
Lowest Power Fully Differential
Quiescent current 1.14 mA/ch
RRO, 145MHz BW
THS770006
*Highest Linearity
ADC Driver*
1.8 GHz Bandwidth
50dB OIP3, 107Mhz IMD3 @ 100MHz



Industrial Amplifiers

DRV8402
*Highest Power
Integrated Driver*
5A RMS / 12A peak Per Bridge
OPA564
*Ideal for OFDM Power Line
Communications*
1.5A Out, 24V, 17MHz
OPA653
Industry's fastest FET Input
2675V/µs Slew Rate
500MHz Bandwidth

OPA836
*Single-ended and
Pseudo differential ADC Driver*
4.6nV/rtHz, 205MHz BW for 1mA I_q
THS3095
Power-Down Capability
I_q 500 µA



Texas
INSTRUMENTS

OPAx333: OPA333 / OPA2333

Lowest Noise | Zero-Drift | Op Amp

Features

- Low Offset Voltage
 - Offset Voltage Drift
 - Very Low Noise
 - Ultra-Low I_Q
 - GBW
 - Supply Voltage
 - Rail-to-Rail Input and Output
 - EMI Input Filter
- | | |
|---------------------------------|---|
| 10 μV (max) | 0.05 $\mu\text{V}/^\circ\text{C}$ (max) |
| 55nV/ $\sqrt{\text{Hz}}$ @ 1kHz | 25 μA (max) |
| 350 kHz | 1.8 V to 5.5 V |

Applications

- Battery Powered Instruments
- Temperature Measurement
- Precision Strain Gages
- Precision Sensor Applications
- Medical Instrumentation
- Handheld Test Equipment


Package Options:

Single: SOIC-8, SON-8, VSSOP-8
Dual: SC70-5, SOT23-5, SOIC-8

Benefits

- 30% Lower Drift than the nearest competitor
- Low offset and drift removes need for calibration
- Lowest Noise among the competition enabling high gain without distortion
- 1.8V Supply and low Quiescent Current make this ideal for portable applications
- RRIO Increases Dynamic Range
- Minimizes EMI induced offset errors
 - Competition doesn't have No zero drift with EMI filtering!

CURRENT AND VOLTAGE NOISE SPECTRAL DENSITY vs FREQUENCY



OPAx188: OPA188 / OPA2188 / OPA4188

0.03 μ V/ $^{\circ}$ C | 6 μ V V_{OS} | 36V | Zero-Drift | Op Amp

Highest-precision,
zero drift,
36V op amp

Features


- GBW 2MHz
- Low Quiescent Current 475 μ A (max)
- Very Low Offset and Drift
 - Offset Voltage 25 μ V (max)
 - Offset Voltage Drift 0.085 μ V/ $^{\circ}$ C max
- CMRR, PSRR, A_{OL} 130dB (min)
- Noise Voltage 8.8nV/ \sqrt Hz at 1kHz
- Noise voltage at 0.1Hz to 10Hz 0.25uVpp
- Supply Range +4.0V to +36V or \pm 2V to \pm 18V
- Rail-to-Rail Output
- EMI/RFI Filtered Inputs
- Input Common Mode Range Extending from Negative Rail to within 1.5V of the Positive Rail

Applications

- Electronic Weigh Scales
- Bridge Amplifier
- Strain Gauge
- Automated Test Equipment
- Transducer amplifier
- Medical Instrumentation
- Resistor Thermal Detector

Benefits

- Improved high accuracy and stability
- Allows for high sensitivity, high resolution systems
- Flexibility in design, enabling low power 5V single supply operation
 - Nearest competitor part's minimum input range is at 1.5V from negative rail, thus no single supply operation is possible
- OPAx188 will have 68% less error caused by input bias current than the nearest competition



Package Options:

Single: SOT23-5, SOIC-8, VSSOP-8

Dual: SOIC-8, VSSOP-8

Quad: TSSOP-14, SOIC-14

[Home](#)[EE](#)[Signal Chain](#)[Power](#)[Technology](#)[Locations](#)[Webench](#)[Investments](#)[Org Chart](#)

Texas
INSTRUMENTS

Data Converter at a glance...

#2 in overall data converter market share with 22%

Low Power

ADC08D1520

3.0 GSPS at only 1.6 W
8-bit ADC for data acquisition

ADS1115

16-bit ADC

Internal Reference
Integrated Oscillator
and Programmable
Comparator @ 0.5mW

ADS4249

**Lowest Power 14-bit
250MSPS ADC**

260mW, lowest by 30%
72.8 dB SNR, 86 dBc SFDR

ADS7924

Ultra Low Power
ADC Monitoring Solution
12b, 4-ch, 4uW/ch @ 1kSPS

DAC161P997

Single Wire Process Automation


16-Bit ADC
4-20mA

DAC34842

Lowest Power 1.25GSPS DAC
4-channel, full feature Tx DAC
Only 250mW / channel

DAC7678

Low Power Octal
8/10/12 bit, I2C in 4x4 QFN
Only 0.28 mW/channel



High Performance

ADC12D1800RF

**Industry's Largest Range
Of Nyquist Sampling**
3.6 GSPS interleaved
1.8 GSPS Dual ADC

ADS1282

Highest Accuracy D/S ADC
32-Bit Resolution w/ on-chip PGA

ADS1675

Highest Bandwidth D/S ADC
24-Bit / 4MSPS
2MHz Input Bandwidth
116 dB SFDR

ADS5493

Highest SFDR 16-bit ADC
16-bit, 130MSPS
97dBc SFDR @90MHz

ADS8486

Lowest Drift 18-Bit ADC
18b fully-differential
1.25MSPS @ 10mW

DAC3283

3G/LTE DAC
16-bit, 800MSPS
ACLR: 81dBc @ 153.6MHz

ADS1298

Measurement ADCs

Complete Front End for Biopotential
(ECG) Measurement

AFE7225

Transmit/Receive for SDR

Dual125MSPS ADCs
Dual 250MSPS DACs

LMP91000

Chemical Sensing ADCs

Low Power Solution
2.7V to 5.5 V

High Integration

Home



EE



Signal Chain



Power



Technology



Locations



WeBench



Investments



Org Chart



Texas
INSTRUMENTS

ADS8556

16-Bit | 630/450kSPS | 6ch Simultaneous Sampling SAR w/ Bipolar Inputs

Features


- Best In Class AC/DC Performance
 - 16-Bit, 3 LSB MAX INL
 - 91.5db SNR (typ)
- True bipolar inputs with software selectable input ranges up to $\pm 12V$ and Selectable parallel or serial interface
- Pin Compatible 14 -/12-Bit Versions
- LQFP-64 Package pin compatible with AD7656
 - Only 122mW @ 250kSPS

Benefits

- Excellent performance and external conversion clock for synchronization of multiple devices enables flexible and expandable systems
- Allows easy connectivity to a wide range of inputs , sensors, and host processors
- Allows for an easy upgrade / downgrade path for future designs
- Improved second source to ADI device with >2x faster sampling rate and 3.5db better SNR

Applications

- Power quality and automation
- Protection relays
- Closed loop servo control
- Robotics



ADS1298R


Complete Integrated Analog Front End for ECG Applications

Features

- Fully Integrated **ECG** Solution
 - 8 Low Noise **Programmable Amps**
 - 8 high resolution **ADC's**
 - Test Signals, RLD Amp, Oscillator, Reference
- Outstanding Performance
 - Noise: **5uV p-p** (150Hz BW, G=6)
 - CMRR : **105dB** with G = 6
- **Continuous Lead Off** detect option
- Integrated Respiration Impedance Measurement Circuitry
- Pace Detect Channel Select (HW / SW)
- Low Power
 - **0.75mW/Channel** (typ)
 - Multiple **Power Down** Configurations
 - **Standby (STBY)** Mode Uses 2mW

Benefits

- 95% less PCB space necessary for 8-channel solution over discrete implementation!
- Meets or exceed IEC & AAMI performance requirements.
- Provides immediate notification if electrode becomes disconnected.
- Reduces BOM cost and consumes negligible power compared to discrete impedance measurement solution
- Insures correct measurement even if external pacer is present.
- 95% less power than discrete solutions! Power down and standby options lengthen battery life for Holter and other portable applications.



Applications

- Medical Instrumentation (ECG and EEG) including:
 - Patient monitoring: Holter, event, stress, and vital signs ECG; AED; fetal ECG
 - Bispectral index (BIS), Sleep study monitor
- High-Precision, Simultaneous, Multichannel Signal Acquisition

Packages: 64-ball BGA

AMC1200

Q-100

4kV_{PEAK} Isolated Amplifier

Features

- Certified Galvanic Isolation Barrier
 - 4kV (**4.25kV**) peak Basic isolation
 - UL1777 and IEC60747-5-2 approved
 - 1.2kVpeak continuous working voltage
- $\pm 250\text{mV}$ input voltage range
- Pin-to-pin performance upgrade for HCPL7800 & HCPL7840
- Specified Temperature range: -40 to 105°C

Applications

Shunt-based Current measurement in:

- Motor Control
- Green Energy
- Frequency Inverter Applications
- Uninterruptible Power Supplies




AMC1200B

4.25kV_{PEAK} Isolated Amplifier

Benefits

- Galvanic barrier provides EMI immunity and robust isolation barrier lifetime
- Optimized for direct connection to shunt resistors or other low voltage level signal sources
- Over 90% more linear, 80% less gain drift, at 50% of the power
- Extended industrial range offers additional 20°C of fully specified performance

Packaging options:
SO-8, SOP-8



AMC1200 EVM Available

Home



EE



Signal Chain



Power



Technology



Locations



WeBench



Investments



Org Chart



TEXAS
INSTRUMENTS

Interface at a glance...

[http://interface\(ti.com](http://interface(ti.com)

#1 in interface market share with 23%

12 new interface products introduced in 2011

Consumer/Computing

DS80PCIxxx

Industry's lowest power and longest reach

PCI Express Redrivers

SN75DP126

Dual-Mode DisplayPort

DisplayPort 1:2 Redriver Switch with Integrated TMDS Translator

SN75LVDS83C

Industry's lowest power

flat panel LVDS transmitter for portable solutions

TUSB7340

Industry's first

Certified 4-port SuperSpeed USB Host

TUSB8040

SuperSpeed

4-port USB Hub

XIO2001

Industry's highest performance, smallest footprint

PCI to PCI Express bridge

ISO1050

Industry's first

Isolated CAN transceiver

ISO1176T

Proven reliability

RS485 Transceiver with integrated transformer driver

ISO764xFM

Longest lifetime

High speed and low power 4-Channel Isolators

General Interfaces

TPD1E10B09

Most versatile

General Purpose ESD Solution

TPD12S015/15A/16

Industry's first

Complete HDMI Companion chips w/ DC-DC or load switch

TPD4E001/101

Low-capacitance

4-Channel +/-15-kV ESD Protection Array for High-Speed Data Interfaces

TS3A225E

Autonomous

Audio Switch with Headset Type Detection

TXS0104E

4-Bit Bidirectional

Voltage-Level Translator for Open-Drain and Push-Pull Applications

SN74AVC2T45/245

Dual-bit dual-supply

bus transceiver with configurable voltage translation and 3-state outputs

TUSB7340

Industry's first

Certified 4-port SuperSpeed USB Host

Industrial

SN65HVD17xx

70V Fault Protection, Low Power, and **Widest Common Mode** Range RS-485 Xcvr

SN65HVS882

Industry's first 8-channel, 34V digital-input serializer

TL16C75xC

Industry's best combination of low voltage support and wide pkg variety

Communications/Networking

SN65LVCP408

Superior

Signal integrity performance 8x8 4.25 Gbps Crosspoint Switch

TLK10002

Industry's only discrete

2 Ch Up to 10Gbps Wide data range SerDes

TLK1102E

Longest reach

dual cable equalizer for 11.3Gbps

TLK3134

Industry's only

Combo of SERDES, Adaptive EQ Rx and ref clk jitter cleaner for 4x3.75Gbps

TLK6002

Widest Frequency

Dual-channel transceiver 0.47G-6.25Gbps



DS90UH925/6

FPD-Link III Ser & Des

720p 24b Color with HDCP

DS92LX2121/2

Channel-Link III Ser & Des

1.05 Gbps data + full-duplex control

LMH0376

3G SDI Re-Clocker

only 90mW

LMH0394

SDI Adaptive EQ

3 Gbps, SMPTE compliant

Video Transport

Home



EE



Signal Chain



Power



Technology



Locations



WeBench



Investments



Org Chart



Texas
INSTRUMENTS

SN65HVD888 RS485 Transceiver

250kbps w/ automatic polarity correction

Features

- 5V supply voltage with 10% tolerance
- IEC ESD protection
- **Automatic polarity correction**
- > ±13V survivability on bus pins
- Low quiescent supply current (<800 uA)
- Extended industrial temperature range
- 5V-tolerant D, DE, RE inputs


Benefits

- Low power, fewer supplies
- Reliable in high noise environments
- Prevents system failure in case of mis-wiring
- Survive shorts to wide range of voltages
- Power savings
- Eliminate cooling fans, ease system design
- Compatible with 5V controllers

Applications

- E-Metering Networks
- Industrial Automation
- HVAC Systems
- DMX512-Networks
- Process Control
- Battery-Powered Applications

BLOCK DIAGRAM



Home



EE



Signal Chain



Power



Technology



Locations



WeBench



Investments



Org Chart



Texas
Instrumen



ISO1050 DUB / DW

4kV / 7kV Isolated - 5V CAN

Features

- Industry's first Isolated CAN transceiver
- Meets or Exceeds ISO 11898
- Isolated CAN with **Ultra low loop time**
- **Very Low EME** (Electro-Magnetic Emissions)
- **CMTI > 25 kV/μs**
- Silicon Integrated **SiO₂** Insulation
 - **4kVpk / 2.5kVrms** – DUB
 - **7kVpk / 5kVrms** – DW
- 6.1mm and 8.3mm Clearance packages
- UL1577 ; IEC ; CSA Approval Pending


Applications

- Medical – ISO1050DW
- Motor Control
- Industrial Automation
- DeviceNet™ Data Buses
- SAE J1939 Standard Data Bus Interface
- ISO 11783 Standard Data Bus Interface
- NMEA 2000 Standard Data Bus Interface

Benefits

- Reduce Components and Board Space - 30%
- Meets DeviceNet and CAN timing requirements
- High Speed Isolation allows longer buses – 34%
- Reduces interference with other devices
- **Proven Reliability of SiO₂ Insulation, Stable over Time, Temperature & Moisture**
 - Life Span > 25 years @ 105°C

Part #	Isolation	Temp (C)	Package
ISO1050DUB	4kVpk/2.5kVrms	-55 to 105	SOP-8
ISO1050DW	7kVpk/5kVrms	-55 to 105	SOIC-16



Compatible with 75+ TI Processors with CAN controllers : C2000, TMS470 ARM, LM3Sxxxx, ARM3 Cortex - M3, OMAP3505/3517

[Home](#)[EE](#)[Signal Chain](#)[Power](#)[Technology](#)[Locations](#)[Webench](#)[Investments](#)[Org Chart](#)

TEXAS INSTRUMENTS



Clocks at a glance...

#3 in timing market share with 8.0%
3 new clock products introduced in 2011


Clock Generation

CDCE(L)9xx**Highly flexible / programmable**Up to 230MHz
Up to 4-PLL, 9 Outputs
Spread-Spectrum**CDCS502****SSC-capable for EMI Reduction**Up to 108MHz
Clock Driver / Multiplier
*Replaces 1 XO***CDCM6100x****Highly versatile, ultra-low jitter**

frequency synthesizers

LMK04808**Industry's lowest phase noise**Jitter Cleaner & Clock Generator
125 fs jitter, 1536 MHz and over

Oscillator ICs

CDCM7005**High Performance
Low Phase Noise
Low Skew**
Clock synchronizer**LMK0480x****Industry's Lowest Noise and Jitter**
Clock Conditioner**LMK03806****Ultra-Low Jitter**
Clock generator with 14 outputs

Distribution PLL Buffers

CDCVF2505**Spectrum Compatibility and
Power-Down Mode**PLL Clock Driver for Synchronous
DRAM and General Purpose Apps**CDCVF855****Differential, zero-delay**Up to 220MHz
PLL Clock Driver
5 Outputs
Spread-Spectrum**CDCVF2510A****Phase-Lock Loop Clock Driver**

3.3V with Power Down Mode

Distribution Fan Out Buffers

CDCLVC1310**Highly Flexible LVC MOS buffer
Ultra Low additive Jitter (30fs typ)
Flexible Power Supply range**Up to 10 Outputs
Universal Inputs**LMK00301****Highly Flexible Universal buffer
Low Jitter (<100fs)**
Flexible Power Supply Range
Low Skew**CDCLVP12xx / 21xx****Ultra-low additive jitter
Low Skew**
Up to 2000MHz
Up to 16 Outputs
LVPECL Driver Family

Audio and Sensing at a glance...

#1 in audio market share with 18%

30 new audio products introduced in 2011 with 150 new sensor products from NSC acquisition

Speaker Power Amplifiers

LM48520

Boosted Stereo Class D
Audio Power Amplifier
with Output Speaker
Protection and
Spreadspectrum

TAS5630B

Class-D PurePath™
600W Mono/300W Stereo
Amplifier

TAS5721

**15W Stereo I2S Audio
Amplifier with Headphone**
with Audio Processing and
2.1 Support

TPA2025D1

Boosted class-D speaker amp
With **Battery Tracking**

TPA3118

**30W Stereo Class D
Amplifier with no Heatsink**
4.5V~26V support/
and 1.2 MHz switching

Audio Converters

LM48901

Quad Channel
Spatial Array

PCM5102

High Performance
112dB Stereo DAC with
2Vrms line driver

PCM1794

Industry's Highest Performance
132dB Stereo DAC

TLV320AIC325x

Ultra Low power
Mobile Codecs w/miniDSP

PCM4222

Industry's Highest Performance
124dB SNR Stereo ADC

TLV320AIC3262

High Integration
Mobile Codec w/miniDSP

Small Signal Amplifiers

DRV632

2VRMS line driver
with **Directpath
Technology**

OPA1602/1604

High Performance
Dual and Quad Bipolar-
Input Audio Op-amps

TPA6136A2

25-mW DirectPath™
Stereo Headphone
Amplifier with Pop
Suppression

PCM2912A

Plug and Play
USB Audio Codec

DIX9211

216KHz
Transceiver

INA282-6

Best Combination
High accuracy and high
CMVR

LM57

High Accuracy
Programmable
Temperature Switch

INA3221

Industry's First
Triple channel Current
Shunt Monitor

TMP112



Industry Leading
Temperature accuracy

Audio Interface



**TEXAS
INSTRUMENTS**

TI's Wide Package Portfolio



TI Package Examples

Small Pin-Count Packages



Thin Shrink Small Outline Package (TSSOP)




Small Outline Transistor (SOT)




Small Outline Integrated Circuit (SOIC)



Mini Small Outline Package (MSOP)



Quad Flatpack No Leads (QFN)



MicroStar Jr™ (u*JR)



MicroStarCSP™ (u*CSP)





Wafer Chip Scale Package (WCSP)


Large Pin-Count Packages




Plastic Ball Grid Array (PBGA)




Flip-Chip Ball Grid Array (FC-BGA)
Package Drawing



Package on Package (POP)
Package Drawing



Lidded FC-BGA
Package Drawing



Copper Pillar FC-BGA
Package Drawing

And More...



Thank You!

Home



EE



Signal Chain



Power



Technology



Locations



WeBench



Investments



Org Chart



 TEXAS
INSTRUMENTS